

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274002

Luminaire Tested: P3A13R259830DE010 E3DLP1WH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274002
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-11)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R259830DE010 E3DLP1WH
Description: 3in Adjustable LED luminaire with, R25 optic, 3000K CCT AND, 98CRI , E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 760.0 lumens
Efficiency: N/A
Efficacy: 52.4 lumens/watt
Spacing Criteria (0/90/45): 0.49 / 0.49 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274002

CATALOG NUMBER: P3A13R259830DE010 E3DLP1WH

Luminous Intensity Polar Plot



TEST NUMBER: P1274002

CATALOG NUMBER: P3A13R259830DE010 E3DLP1WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	110	105	102	99	107	104	101	98	101	98	96		98	96	94		95
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91
4	101	95	90	87	99	94	89	86	92	88	85		90	87	84		88
5	97	90	85	82	96	89	85	81	88	84	81		86	83	80		85
6	94	86	81	78	92	86	81	78	84	80	77		83	79	77		82
7	90	83	78	74	89	82	77	74	81	77	74		80	76	73		79
8	87	79	74	71	86	79	74	71	78	74	71		77	73	70		76
9	84	76	71	68	83	76	71	68	75	71	68		74	70	68		73
10	81	73	69	65	80	73	68	65	72	68	65		72	68	65		71

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	487505
5°	454830
10°	364366
15°	247334
20°	149650
25°	87513
30°	49830
35°	27412
40°	14542
45°	7660
50°	4469
55°	3326
60°	2851
65°	3009
70°	2821
75°	2457
80°	1894
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 7660 cd/sqm

TEST NUMBER: P1274002

CATALOG NUMBER: P3A13R259830DE010 E3DLP1WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	183.4	24.1
10°-20°	299.5	39.4
20°-30°	171.1	22.5
30°-40°	67.5	8.9
40°-50°	20.7	2.7
50°-60°	8.2	1.1
60°-70°	5.5	0.7
70°-80°	3.1	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	654.0	86.1
0°-40°	721.6	94.9
0°-60°	750.5	98.7
0°-90°	760.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	760.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2223	
5°	2066	183
15°	1090	300
25°	362	171
35°	102	68
45°	25	21
55°	9	8
65°	6	5
75°	3	3
85°	1	1
90°	0	

TEST NUMBER: P1274002

CATALOG NUMBER: P3A13R259830DE010 E3DLP1WH

CANDELA DISTRIBUTION (FULL):

0°	
0°	2223.2
1°	2218.9
2°	2200.7
3°	2168.8
4°	2124.5
5°	2066.3
6°	1998.1
7°	1921.1
8°	1831.8
9°	1740.2
10°	1636.4
11°	1534.0
12°	1421.4
13°	1310.3
14°	1196.2
15°	1089.5
17.5°	844.7
20°	641.3
22.5°	481.5
25°	361.7
27.5°	268.0
30°	196.8
32.5°	142.4
35°	102.4
37.5°	72.6
40°	50.8
42.5°	34.9
45°	24.7
47.5°	17.4
50°	13.1
52.5°	10.2
55°	8.7
57.5°	8.0
60°	6.5
62.5°	5.8
65°	5.8
67.5°	5.1
70°	4.4
72.5°	3.6
75°	2.9
77.5°	2.2
80°	1.5
82.5°	1.5
85°	0.7
87.5°	0.7



TEST NUMBER: P1274002

CATALOG NUMBER: P3A13R259830DE010 E3DLP1WH

CANDELA DISTRIBUTION (continued):



(END OF REPORT)