

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274116

Luminaire Tested: P3A13R459830DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274116
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R459830DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R45 optic, 3000K CCT AND, 98CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 523.0 lumens
Efficiency: N/A
Efficacy: 36.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274116
CATALOG NUMBER: P3A13R459830DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1274116
 CATALOG NUMBER: P3A13R459830DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	93				93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	86				86
3	102	95	90	85	100	93	89	85	91	87	83	88	85	82	86	83	81	79				79
4	96	88	83	78	94	87	82	78	85	81	77	83	79	76	81	78	75	74				74
5	91	83	77	72	90	82	76	72	80	75	71	78	74	71	77	73	70	69				69
6	87	78	72	67	85	77	71	67	75	70	66	74	69	66	73	69	66	64				64
7	83	73	67	63	81	72	67	63	71	66	62	70	65	62	69	65	61	60				60
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	56				56
9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53				53
10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50				50

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	155777
5°	152234
10°	140434
15°	122112
20°	100319
25°	78053
30°	57629
35°	40555
40°	25305
45°	13707
50°	7403
55°	6384
60°	5701
65°	4877
70°	4167
75°	4321
80°	3662
85°	3522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13707 cd/sqm



TEST NUMBER: P1274116
 CATALOG NUMBER: P3A13R459830DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.1	12.2
10°-20°	148.7	28.4
20°-30°	147.6	28.2
30°-40°	95.1	18.2
40°-50°	36.6	7.0
50°-60°	14.9	2.8
60°-70°	9.4	1.8
70°-80°	5.1	1.0
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.4	68.9
0°-40°	455.4	87.1
0°-60°	506.9	96.9
0°-90°	523.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	523.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	710	
5°	692	64
15°	538	149
25°	323	148
35°	152	95
45°	44	37
55°	17	15
65°	9	9
75°	5	5
85°	1	2
90°	0	

TEST NUMBER: P1274116

CATALOG NUMBER: P3A13R459830DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	710.4
2.5°	706.8
5°	691.6
7.5°	665.5
10°	630.7
12.5°	587.2
15°	537.9
17.5°	484.2
20°	429.9
22.5°	374.8
25°	322.6
27.5°	273.3
30°	227.6
32.5°	187.8
35°	151.5
37.5°	118.9
40°	88.4
42.5°	63.8
45°	44.2
47.5°	29.7
50°	21.7
52.5°	18.1
55°	16.7
57.5°	14.5
60°	13.0
62.5°	10.9
65°	9.4
67.5°	8.0
70°	6.5
72.5°	5.8
75°	5.1
77.5°	3.6
80°	2.9
82.5°	2.2
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)