

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274123

Luminaire Tested: P3A13R509830DE010 E3CB1MW

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1274123  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R509830DE010 E3CB1MW  
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 993.0 lumens  
Efficiency: N/A  
Efficacy: 68.5 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274123  
CATALOG NUMBER: P3A13R509830DE010 E3CB1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P1274123

CATALOG NUMBER: P3A13R509830DE010 E3CB1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95	95	95	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90	90	90	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	92	88	85	90	87	84	88	85	83	87	84	82	80	80	80	80
5	96	89	84	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76	76	76	76
6	92	84	79	75	91	83	79	75	82	78	74	81	77	74	79	76	73	72	72	72	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
8	85	76	71	67	83	76	71	67	75	70	67	74	70	67	73	69	66	65	65	65	65
9	81	73	68	64	80	72	67	64	71	67	64	71	66	63	70	66	63	62	62	62	62
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	59	59	59	59

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	345828
5°	339643
10°	326113
15°	299048
20°	263690
25°	202125
30°	109890
35°	35362
40°	8301
45°	1116
50°	989
55°	1109
60°	965
65°	1141
70°	962
75°	1271
80°	884
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 85°  
 Luminance: 1761 cd/sqm



TEST NUMBER: P1274123  
 CATALOG NUMBER: P3A13R509830DE010 E3CB1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	144.8	14.6
10°-20°	366.2	36.9
20°-30°	366.7	36.9
30°-40°	103.1	10.4
40°-50°	6.2	0.6
50°-60°	2.4	0.2
60°-70°	1.9	0.2
70°-80°	1.3	0.1
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	877.7	88.4
0°-40°	980.8	98.8
0°-60°	989.4	99.6
0°-90°	993.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	993.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1577	
5°	1543	145
15°	1317	366
25°	835	367
35°	132	103
45°	4	6
55°	3	2
65°	2	2
75°	2	1
85°	1	0
90°	0	



TEST NUMBER: P1274123  
CATALOG NUMBER: P3A13R509830DE010 E3CB1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1577.1
2.5°	1569.1
5°	1543.0
7.5°	1507.4
10°	1464.6
12.5°	1400.0
15°	1317.3
17.5°	1222.2
20°	1130.0
22.5°	1015.4
25°	835.4
27.5°	622.0
30°	434.0
32.5°	262.0
35°	132.1
37.5°	62.4
40°	29.0
42.5°	10.9
45°	3.6
47.5°	2.9
50°	2.9
52.5°	2.9
55°	2.9
57.5°	2.2
60°	2.2
62.5°	2.2
65°	2.2
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.7
80°	0.7
82.5°	0.7
85°	0.7
87.5°	0.0
90°	0.0

(END OF REPORT)