

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274140

Luminaire Tested: P3A13R509830DE010 E3DLD1LI

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274140
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-30)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R509830DE010 E3DLD1LI
Description: 3in Adjustable LED luminaire with, R50 optic, 3000K CCT AND, 98CRI , E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 636.0 lumens
Efficiency: N/A
Efficacy: 43.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.93
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274140

CATALOG NUMBER: P3A13R509830DE010 E3DLD1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1274140

CATALOG NUMBER: P3A13R509830DE010 E3DLD1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	112	109	106	103	110	107	104	102	103	101	99		99	97	96		95
2	106	100	95	91	103	98	94	90	95	91	88		92	89	86		89
3	99	92	86	81	97	90	85	81	88	83	79		85	81	78		83
4	93	85	78	73	91	83	77	73	81	76	72		79	75	71		77
5	88	78	72	67	86	77	71	66	75	70	66		74	69	65		72
6	83	73	66	61	81	72	65	61	70	65	60		69	64	60		67
7	78	68	61	56	77	67	61	56	66	60	56		64	59	55		63
8	74	63	57	52	73	63	56	52	61	56	52		60	55	51		59
9	70	59	53	48	69	59	52	48	58	52	48		57	52	48		56
10	66	56	49	45	65	55	49	45	54	49	45		54	48	45		53

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	129244
5°	127338
10°	121708
15°	112713
20°	101299
25°	89037
30°	75733
35°	61409
40°	46115
45°	29709
50°	14123
55°	11087
60°	10525
65°	9806
70°	8848
75°	7964
80°	7324
85°	7296

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 29709 cd/sqm

TEST NUMBER: P1274140

CATALOG NUMBER: P3A13R509830DE010 E3DLD1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	54.2	8.5
10°-20°	138.4	21.8
20°-30°	168.2	26.4
30°-40°	142.6	22.4
40°-50°	74.1	11.6
50°-60°	26.7	4.2
60°-70°	18.5	2.9
70°-80°	10.0	1.6
80°-90°	3.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	360.8	56.7
0°-40°	503.5	79.2
0°-60°	604.3	95.0
0°-90°	636.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	636.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	589	
5°	578	54
15°	496	138
25°	368	168
35°	229	143
45°	96	74
55°	29	27
65°	19	19
75°	9	10
85°	3	3
90°	0	

TEST NUMBER: P1274140

CATALOG NUMBER: P3A13R509830DE010 E3DLD1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	589.4
2.5°	587.2
5°	578.5
7.5°	565.5
10°	546.6
12.5°	522.6
15°	496.5
17.5°	466.7
20°	434.1
22.5°	400.7
25°	368.0
27.5°	333.9
30°	299.1
32.5°	264.2
35°	229.4
37.5°	195.3
40°	161.1
42.5°	128.5
45°	95.8
47.5°	63.9
50°	41.4
52.5°	31.9
55°	29.0
57.5°	26.1
60°	24.0
62.5°	21.1
65°	18.9
67.5°	16.0
70°	13.8
72.5°	11.6
75°	9.4
77.5°	7.3
80°	5.8
82.5°	4.4
85°	2.9
87.5°	1.5
90°	0.0

(END OF REPORT)