

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274194

Luminaire Tested: P3A13R609830DE010 E3DL1WH

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1274194  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R609830DE010 E3DL1WH  
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3DL1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 528.0 lumens  
Efficiency: N/A  
Efficacy: 36.4 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274194  
CATALOG NUMBER: P3A13R609830DE010 E3DL1WH

### Luminous Intensity Polar Plot





TEST NUMBER: P1274194  
 CATALOG NUMBER: P3A13R609830DE010 E3DL1WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92			
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85			
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78			
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72			
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66			
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62			
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	57			
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	133805
5°	130816
10°	122465
15°	109876
20°	94485
25°	78125
30°	61731
35°	45829
40°	31573
45°	19816
50°	10882
55°	6384
60°	5745
65°	4877
70°	4167
75°	4321
80°	3662
85°	3774

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 19816 cd/sqm



TEST NUMBER: P1274194  
 CATALOG NUMBER: P3A13R609830DE010 E3DL1WH

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	55.3	10.5
10°-20°	134.4	25.5
20°-30°	147.4	27.9
30°-40°	107.4	20.3
40°-50°	50.7	9.6
50°-60°	16.6	3.1
60°-70°	9.4	1.8
70°-80°	5.1	1.0
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	337.2	63.9
0°-40°	444.6	84.2
0°-60°	511.9	97.0
0°-90°	528.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	528.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	610	
5°	594	55
15°	484	134
25°	323	147
35°	171	107
45°	64	51
55°	17	17
65°	9	9
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1274194  
CATALOG NUMBER: P3A13R609830DE010 E3DL1WH

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	610.2
2.5°	606.6
5°	594.3
7.5°	575.4
10°	550.0
12.5°	519.5
15°	484.0
17.5°	445.5
20°	404.9
22.5°	363.5
25°	322.9
27.5°	282.3
30°	243.8
32.5°	206.8
35°	171.2
37.5°	139.3
40°	110.3
42.5°	84.9
45°	63.9
47.5°	46.4
50°	31.9
52.5°	21.0
55°	16.7
57.5°	14.5
60°	13.1
62.5°	10.9
65°	9.4
67.5°	8.0
70°	6.5
72.5°	5.8
75°	5.1
77.5°	3.6
80°	2.9
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)