

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274202

Luminaire Tested: P3A13R609830DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274202
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R609830DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 259.0 lumens
Efficiency: N/A
Efficacy: 17.9 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274202

CATALOG NUMBER: P3A13R609830DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1274202

CATALOG NUMBER: P3A13R609830DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92		
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85		
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78		
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	72		
5	90	81	75	70	88	80	74	70	78	73	69	77	72	69	75	71	68	66		
6	85	76	69	65	84	75	69	65	73	68	64	72	67	64	71	66	63	62		
7	81	71	65	60	79	70	64	60	69	64	60	68	63	59	67	62	59	58		
8	77	67	60	56	75	66	60	56	65	60	56	64	59	55	63	58	55	54		
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50		
10	69	59	53	49	68	59	53	49	58	53	49	57	52	49	56	52	49	47		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	65631
5°	64164
10°	60075
15°	53894
20°	46344
25°	38325
30°	30283
35°	22486
40°	15486
45°	9706
50°	5356
55°	3135
60°	2807
65°	2387
70°	2052
75°	2118
80°	1768
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 9706 cd/sqm

TEST NUMBER: P1274202

CATALOG NUMBER: P3A13R609830DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.1	10.5
10°-20°	65.9	25.5
20°-30°	72.3	27.9
30°-40°	52.7	20.3
40°-50°	24.9	9.6
50°-60°	8.1	3.1
60°-70°	4.6	1.8
70°-80°	2.5	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	165.4	63.9
0°-40°	218.1	84.2
0°-60°	251.1	97.0
0°-90°	259.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	259.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	299	
5°	292	27
15°	237	66
25°	158	72
35°	84	53
45°	31	25
55°	8	8
65°	5	5
75°	2	2
85°	1	1
90°	0	

TEST NUMBER: P1274202

CATALOG NUMBER: P3A13R609830DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	299.3
2.5°	297.6
5°	291.5
7.5°	282.3
10°	269.8
12.5°	254.8
15°	237.4
17.5°	218.5
20°	198.6
22.5°	178.3
25°	158.4
27.5°	138.5
30°	119.6
32.5°	101.4
35°	84.0
37.5°	68.3
40°	54.1
42.5°	41.6
45°	31.3
47.5°	22.8
50°	15.7
52.5°	10.3
55°	8.2
57.5°	7.1
60°	6.4
62.5°	5.3
65°	4.6
67.5°	3.9
70°	3.2
72.5°	2.8
75°	2.5
77.5°	1.8
80°	1.4
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)