

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274203

Luminaire Tested: P3A13R609830DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274203
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R609830DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R60 optic, 3000K CCT AND, 98CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 528.0 lumens
Efficiency: N/A
Efficacy: 36.4 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274203

CATALOG NUMBER: P3A13R609830DE010 E3DLP1H

Luminous Intensity Polar Plot



TEST NUMBER: P1274203

CATALOG NUMBER: P3A13R609830DE010 E3DLP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	133805
5°	130816
10°	122465
15°	109876
20°	94485
25°	78125
30°	61731
35°	45829
40°	31573
45°	19816
50°	10882
55°	6384
60°	5745
65°	4877
70°	4167
75°	4321
80°	3662
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19816 cd/sqm

TEST NUMBER: P1274203

CATALOG NUMBER: P3A13R609830DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.3	10.5
10°-20°	134.4	25.5
20°-30°	147.4	27.9
30°-40°	107.4	20.3
40°-50°	50.7	9.6
50°-60°	16.6	3.1
60°-70°	9.4	1.8
70°-80°	5.1	1.0
80°-90°	1.6	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	337.2	63.9
0°-40°	444.6	84.2
0°-60°	511.9	97.0
0°-90°	528.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	528.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	610	
5°	594	55
15°	484	134
25°	323	147
35°	171	107
45°	64	51
55°	17	17
65°	9	9
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1274203

CATALOG NUMBER: P3A13R609830DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	610.2
2.5°	606.6
5°	594.3
7.5°	575.4
10°	550.0
12.5°	519.5
15°	484.0
17.5°	445.5
20°	404.9
22.5°	363.5
25°	322.9
27.5°	282.3
30°	243.8
32.5°	206.8
35°	171.2
37.5°	139.3
40°	110.3
42.5°	84.9
45°	63.9
47.5°	46.4
50°	31.9
52.5°	21.0
55°	16.7
57.5°	14.5
60°	13.1
62.5°	10.9
65°	9.4
67.5°	8.0
70°	6.5
72.5°	5.8
75°	5.1
77.5°	3.6
80°	2.9
82.5°	2.2
85°	1.5
87.5°	0.7
90°	0.0

(END OF REPORT)