

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274227

Luminaire Tested: P3A13R659830DE010 E3DLD1LI

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1274227  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-42)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R659830DE010 E3DLD1LI  
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 98CRI , E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 572.0 lumens  
Efficiency: N/A  
Efficacy: 39.5 lumens/watt  
Spacing Criteria (0/90/45): 0.94 / 0.94 / 1  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1274227  
CATALOG NUMBER: P3A13R659830DE010 E3DLD1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P1274227  
 CATALOG NUMBER: P3A13R659830DE010 E3DLD1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	112	109	106	103	110	107	104	101	102	100	98	99	97	95	95	94	93	91			
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	86	84	82			
3	99	91	85	80	96	89	84	79	87	82	78	84	80	77	82	78	76	74			
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67			
5	87	77	70	65	85	76	69	65	74	68	64	72	67	63	71	66	63	61			
6	82	71	64	59	80	70	64	59	69	63	58	67	62	58	66	61	58	56			
7	77	66	59	54	75	65	59	54	64	58	54	63	57	53	61	57	53	51			
8	72	61	55	50	71	61	54	50	60	54	49	59	53	49	58	53	49	47			
9	68	57	51	46	67	57	50	46	56	50	46	55	49	46	54	49	45	44			
10	65	54	47	43	64	53	47	43	52	47	43	52	46	42	51	46	42	41			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	101790
5°	100418
10°	97059
15°	91533
20°	84427
25°	76625
30°	67884
35°	57768
40°	45943
45°	32437
50°	18831
55°	10284
60°	9561
65°	8665
70°	7886
75°	7371
80°	6440
85°	5535

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 32437 cd/sqm



TEST NUMBER: P1274227  
 CATALOG NUMBER: P3A13R659830DE010 E3DLD1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.9	7.5
10°-20°	112.8	19.7
20°-30°	145.0	25.3
30°-40°	134.1	23.4
40°-50°	80.9	14.2
50°-60°	27.6	4.8
60°-70°	16.6	2.9
70°-80°	9.4	1.6
80°-90°	2.7	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	300.7	52.6
0°-40°	434.8	76.0
0°-60°	543.4	95.0
0°-90°	572.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	572.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	464	
5°	456	43
15°	403	113
25°	317	145
35°	216	134
45°	105	81
55°	27	28
65°	17	17
75°	9	9
85°	2	3
90°	0	

TEST NUMBER: P1274227  
CATALOG NUMBER: P3A13R659830DE010 E3DLD1LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	464.2
2.5°	462.0
5°	456.2
7.5°	447.5
10°	435.9
12.5°	421.3
15°	403.2
17.5°	383.6
20°	361.8
22.5°	339.3
25°	316.7
27.5°	292.8
30°	268.1
32.5°	243.4
35°	215.8
37.5°	188.9
40°	160.5
42.5°	132.2
45°	104.6
47.5°	79.2
50°	55.2
52.5°	34.9
55°	26.9
57.5°	24.0
60°	21.8
62.5°	18.9
65°	16.7
67.5°	14.5
70°	12.3
72.5°	10.9
75°	8.7
77.5°	7.3
80°	5.1
82.5°	3.6
85°	2.2
87.5°	1.5
90°	0.0

(END OF REPORT)