

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274285

Luminaire Tested: P3A17R159830DE010 E3DLP1GPH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274285
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R159830DE010 E3DLP1GPH
Description: 3in Adjustable LED luminaire with, R15 optic, 3000K CCT AND, 98CRI , E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 355.0 lumens
Efficiency: N/A
Efficacy: 17.4 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274285

CATALOG NUMBER: P3A17R159830DE010 E3DLP1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1274285

CATALOG NUMBER: P3A17R159830DE010 E3DLP1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	113	110	108	106		111	108	106	104		104	102	101		100	99	98		97	96	95
2	108	103	98	95		105	101	97	94		98	95	92		95	92	90		92	90	88
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77
5	93	84	78	74		91	83	78	74		81	77	73		80	76	72		78	75	72
6	88	79	73	69		87	79	73	69		77	72	69		76	71	68		74	71	68
7	84	75	69	65		83	74	69	65		73	68	64		72	67	64		71	67	64
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		67	63	60
9	77	68	62	58		76	67	62	58		66	61	58		65	61	57		64	60	57
10	74	64	59	55		73	64	59	55		63	58	55		62	58	55		62	57	54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	153080
5°	141492
10°	112957
15°	85335
20°	64966
25°	49527
30°	35474
35°	23155
40°	14198
45°	8590
50°	5697
55°	4396
60°	3772
65°	3269
70°	2949
75°	2965
80°	2147
85°	1510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 8590 cd/sqm

TEST NUMBER: P1274285

CATALOG NUMBER: P3A17R159830DE010 E3DLP1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.9	16.0
10°-20°	105.1	29.6
20°-30°	93.5	26.3
30°-40°	55.3	15.6
40°-50°	22.7	6.4
50°-60°	10.6	3.0
60°-70°	6.5	1.8
70°-80°	3.4	1.0
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	255.5	72.0
0°-40°	310.9	87.6
0°-60°	344.2	97.0
0°-90°	355.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	355.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	698	
5°	643	57
15°	376	105
25°	205	94
35°	86	55
45°	28	23
55°	12	11
65°	6	6
75°	4	3
85°	1	1
90°	0	

TEST NUMBER: P1274285

CATALOG NUMBER: P3A17R159830DE010 E3DLP1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	698.1
1°	696.4
2°	691.2
3°	680.8
4°	663.5
5°	642.8
6°	620.3
7°	593.8
8°	566.1
9°	537.9
10°	507.3
12.5°	437.5
15°	375.9
17.5°	322.8
20°	278.4
22.5°	239.2
25°	204.7
27.5°	171.2
30°	140.1
32.5°	111.8
35°	86.5
37.5°	66.3
40°	49.6
42.5°	36.9
45°	27.7
47.5°	21.3
50°	16.7
52.5°	13.8
55°	11.5
57.5°	9.8
60°	8.6
62.5°	7.5
65°	6.3
67.5°	5.8
70°	4.6
72.5°	4.0
75°	3.5
77.5°	2.3
80°	1.7
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)