

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1274301

Luminaire Tested: P3A17R209830DE010 E3D1LI

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1274301
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-8)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17R209830DE010 E3D1LI
Description: 3in Adjustable LED luminaire with, R20 optic, 3000K CCT AND, 98CRI , E3D1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1473.0 lumens
Efficiency: N/A
Efficacy: 72.2 lumens/watt
Spacing Criteria (0/90/45): 0.35 / 0.35 / 0.34
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1274301

CATALOG NUMBER: P3A17R209830DE010 E3D1LI

Luminous Intensity Polar Plot



TEST NUMBER: P1274301

CATALOG NUMBER: P3A17R209830DE010 E3D1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	115	114	112	110		113	111	110	108		107	106	105		104	103	102		100	100	99
2	112	109	106	104		110	107	105	103		104	102	101		101	100	98		99	98	96
3	109	105	102	99		107	104	101	98		101	99	97		99	97	95		97	95	94
4	106	101	98	95		105	100	97	95		99	96	94		97	95	93		95	93	92
5	104	98	95	92		102	98	94	92		96	93	91		95	92	90		93	91	90
6	101	96	92	89		100	95	92	89		94	91	89		93	90	88		92	89	88
7	99	93	90	87		98	93	89	87		92	89	86		91	88	86		90	87	86
8	97	91	87	85		96	91	87	85		90	87	85		89	86	84		88	86	84
9	95	89	85	83		94	89	85	83		88	85	83		87	84	83		87	84	82
10	93	87	84	81		92	87	83	81		86	83	81		86	83	81		85	83	81

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	2234426
5°	1881285
10°	1175039
15°	439299
20°	150793
25°	62834
30°	29599
35°	13251
40°	6269
45°	3225
50°	1194
55°	229
60°	263
65°	311
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3225 cd/sqm

TEST NUMBER: P1274301

CATALOG NUMBER: P3A17R209830DE010 E3D1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	710.7	48.2
10°-20°	585.4	39.7
20°-30°	133.0	9.0
30°-40°	33.9	2.3
40°-50°	8.5	0.6
50°-60°	1.1	0.1
60°-70°	0.4	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1429.2	97.0
0°-40°	1463.1	99.3
0°-60°	1472.7	100.0
0°-90°	1473.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1473.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10190	
5°	8547	711
15°	1935	585
25°	260	133
35°	50	34
45°	10	9
55°	1	1
65°	1	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1274301

CATALOG NUMBER: P3A17R209830DE010 E3D1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	10189.8
1°	10103.4
2°	9848.8
3°	9483.7
4°	9035.6
5°	8546.7
6°	8001.9
7°	7400.6
8°	6699.1
9°	6004.0
10°	5277.2
11°	4503.7
12°	3731.4
13°	3077.1
14°	2451.7
15°	1935.1
16°	1527.3
17°	1204.8
18°	968.1
19°	787.3
20°	646.2
21°	540.2
22°	450.9
23°	374.9
24°	312.7
25°	259.7
27.5°	169.9
30°	116.9
32.5°	72.0
35°	49.5
37.5°	31.7
40°	21.9
42.5°	15.0
45°	10.4
47.5°	6.9
50°	3.5
52.5°	1.7
55°	0.6
57.5°	0.6
60°	0.6
62.5°	0.6
65°	0.6
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P1274301
CATALOG NUMBER: P3A17R209830DE010 E3D1LI

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)