

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426596

Luminaire Tested: P3A13RH9835DE010 E3HY1GPH

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426596
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-6)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13RH9835DE010 E3HY1GPH
Description: 3in Adjustable LED luminaire with, RH optic, 3500K CCT AND, 98CRI , E3HY1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 270.0 lumens
Efficiency: N/A
Efficacy: 18.6 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 14.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426596

CATALOG NUMBER: P3A13RH9835DE010 E3HY1GPH

Luminous Intensity Polar Plot



TEST NUMBER: P1426596

CATALOG NUMBER: P3A13RH9835DE010 E3HY1GPH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96			
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	92			
3	107	102	98	95	105	101	97	95	98	95	93	96	94	92	94	92	90	89			
4	103	98	94	90	102	97	93	90	95	91	89	93	90	88	91	89	87	86			
5	100	94	89	86	99	93	89	86	91	88	85	90	87	84	88	86	84	83			
6	97	90	86	83	96	89	85	82	88	84	82	87	84	81	86	83	81	80			
7	94	87	82	79	93	86	82	79	85	81	79	84	81	78	83	80	78	77			
8	91	84	79	76	90	83	79	76	82	79	76	81	78	76	81	78	75	74			
9	88	81	77	74	87	81	76	74	80	76	73	79	76	73	78	75	73	72			
10	85	78	74	71	85	78	74	71	77	73	71	77	73	71	76	73	71	70			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	183319
5°	167356
10°	144998
15°	127560
20°	55491
25°	21243
30°	14382
35°	4872
40°	1517
45°	465
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 465 cd/sqm

TEST NUMBER: P1426596

CATALOG NUMBER: P3A13RH9835DE010 E3HY1GPH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.9	25.5
10°-20°	138.3	51.2
20°-30°	46.9	17.4
30°-40°	14.3	5.3
40°-50°	1.5	0.6
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.2	94.1
0°-40°	268.5	99.4
0°-60°	270.0	100.0
0°-90°	270.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	270.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	836	
5°	760	69
15°	562	138
25°	88	47
35°	18	14
45°	2	1
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426596

CATALOG NUMBER: P3A13RH9835DE010 E3HY1GPH

CANDELA DISTRIBUTION (FULL):

0°	
0°	836.0
2.5°	817.8
5°	760.3
7.5°	696.7
10°	651.2
12.5°	610.3
15°	561.9
17.5°	417.2
20°	237.8
22.5°	115.9
25°	87.8
27.5°	71.2
30°	56.8
32.5°	36.3
35°	18.2
37.5°	9.8
40°	5.3
42.5°	3.0
45°	1.5
47.5°	0.8
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)