

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1344087

Luminaire Tested: P3A13R209840DE010 E3A301GPH

Issue Date: 2/13/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1344087  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-60)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/13/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R209840DE010 E3A301GPH  
Description: 3in Adjustable LED luminaire with, R20 optic, 4000K CCT AND, 98CRI , E3A301GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 378.9 lumens  
Efficiency: N/A  
Efficacy: 26.1 lumens/watt  
Spacing Criteria (0/90/45): 2.29 / 0.53 / 1.19  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1344087

CATALOG NUMBER: P3A13R209840DE010 E3A301GPH

### Luminous Intensity Polar Plot



TEST NUMBER: P1344087

CATALOG NUMBER: P3A13R209840DE010 E3A301GPH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 | 100 |
| 1   | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  |  | 99  | 98  | 96  |  | 96  | 95  | 93  | 92  |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 94  | 91  | 95  | 92  | 89  |  | 92  | 89  | 87  |  | 89  | 87  | 85  | 83  |
| 3   | 99  | 92  | 86  | 81  | 97  | 90  | 85  | 81  | 88  | 83  | 79  |  | 85  | 81  | 78  |  | 83  | 80  | 77  | 75  |
| 4   | 93  | 84  | 78  | 73  | 91  | 83  | 77  | 72  | 81  | 76  | 71  |  | 79  | 74  | 71  |  | 77  | 73  | 70  | 68  |
| 5   | 87  | 77  | 70  | 65  | 85  | 76  | 70  | 65  | 74  | 69  | 64  |  | 72  | 68  | 64  |  | 71  | 67  | 63  | 61  |
| 6   | 81  | 71  | 64  | 59  | 80  | 70  | 63  | 58  | 68  | 62  | 58  |  | 67  | 62  | 58  |  | 65  | 61  | 57  | 55  |
| 7   | 76  | 65  | 58  | 53  | 74  | 64  | 57  | 53  | 63  | 57  | 52  |  | 62  | 56  | 52  |  | 60  | 55  | 52  | 50  |
| 8   | 71  | 60  | 53  | 48  | 70  | 59  | 52  | 48  | 58  | 52  | 47  |  | 57  | 51  | 47  |  | 56  | 51  | 47  | 45  |
| 9   | 66  | 55  | 48  | 43  | 65  | 54  | 48  | 43  | 53  | 47  | 43  |  | 52  | 47  | 43  |  | 51  | 46  | 43  | 41  |
| 10  | 62  | 51  | 44  | 39  | 61  | 50  | 44  | 39  | 49  | 43  | 39  |  | 48  | 43  | 39  |  | 48  | 42  | 39  | 37  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°     | 45°   | 90°  | 135° | 180° |
|-----|--------|-------|------|------|------|
| 0°  | 2873   | 2873  | 2873 | 2873 | 2873 |
| 5°  | 6582   | 4909  | 2729 | 1673 | 1431 |
| 10° | 20752  | 8573  | 2227 | 913  | 690  |
| 15° | 134416 | 15846 | 1635 | 318  | 68   |
| 20° | 405685 | 27116 | 1120 | 0    | 0    |
| 25° | 602478 | 27364 | 677  | 0    | 0    |
| 30° | 677522 | 20813 | 253  | 0    | 0    |
| 35° | 584560 | 12421 | 187  | 0    | 0    |
| 40° | 336602 | 4237  | 0    | 0    | 0    |
| 45° | 82117  | 1706  | 93   | 0    | 93   |
| 50° | 9859   | 478   | 102  | 102  | 341  |
| 55° | 1300   | 0     | 268  | 268  | 535  |
| 60° | 132    | 0     | 439  | 439  | 746  |
| 65° | 156    | 156   | 726  | 726  | 1090 |
| 70° | 192    | 192   | 898  | 898  | 1090 |
| 75° | 0      | 254   | 1186 | 847  | 1186 |
| 80° | 0      | 379   | 1263 | 884  | 1263 |
| 85° | 0      | 755   | 2516 | 755  | 755  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 2.5°

Vertical Angle: 45°

Luminance: 82644 cd/sqm

TEST NUMBER: P1344087

CATALOG NUMBER: P3A13R209840DE010 E3A301GPH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1.7    | 0.5       |
| 10°-20°   | 35.1   | 9.3       |
| 20°-30°   | 153.1  | 40.4      |
| 30°-40°   | 154.2  | 40.7      |
| 40°-50°   | 30.9   | 8.2       |
| 50°-60°   | 1.5    | 0.4       |
| 60°-70°   | 1.0    | 0.3       |
| 70°-80°   | 0.9    | 0.2       |
| 80°-90°   | 0.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 190.0  | 50.1      |
| 0°-40°    | 344.1  | 90.8      |
| 0°-60°    | 376.6  | 99.4      |
| 0°-90°    | 378.9  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 378.9  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 45° | 90° | 135° | 180° | Flux |
|-----|------|-----|-----|------|------|------|
| 0°  | 13   | 13  | 13  | 13   | 13   |      |
| 5°  | 30   | 22  | 12  | 8    | 6    | 5    |
| 15° | 592  | 70  | 7   | 1    | 0    | 232  |
| 25° | 2490 | 113 | 3   | 0    | 0    | 1123 |
| 35° | 2184 | 46  | 1   | 0    | 0    | 1299 |
| 45° | 265  | 6   | 0   | 0    | 0    | 288  |
| 55° | 3    | 0   | 1   | 1    | 1    | 6    |
| 65° | 0    | 0   | 1   | 1    | 2    | 0    |
| 75° | 0    | 0   | 1   | 1    | 1    | 0    |
| 85° | 0    | 0   | 1   | 0    | 0    | 0    |
| 90° | 0    | 0   | 0   | 0    | 0    |      |

TEST NUMBER: P1344087

CATALOG NUMBER: P3A13R209840DE010 E3A301GPH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5°  | 45°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|--------|-------|
| 0°    | 13.1   | 13.1   | 13.1   | 13.1   | 13.1   | 13.1   | 13.1   | 13.1   | 13.1   | 13.1   | 13.1  |
| 2.5°  | 19.6   | 19.6   | 19.3   | 19.3   | 18.9   | 19.3   | 18.6   | 18.9   | 18.9   | 18.6   | 16.8  |
| 5°    | 29.9   | 30.6   | 30.3   | 30.3   | 29.9   | 30.3   | 29.6   | 28.9   | 28.2   | 28.2   | 22.3  |
| 7.5°  | 49.2   | 48.8   | 48.1   | 48.5   | 47.5   | 46.8   | 46.1   | 45.7   | 43.7   | 42.6   | 29.2  |
| 10°   | 93.2   | 95.2   | 93.5   | 93.2   | 87.0   | 86.6   | 82.5   | 76.7   | 71.5   | 68.8   | 38.5  |
| 12.5° | 256.5  | 267.5  | 250.3  | 242.1  | 237.3  | 218.7  | 210.8  | 190.5  | 170.9  | 156.1  | 48.8  |
| 15°   | 592.1  | 619.3  | 584.5  | 586.9  | 558.1  | 505.1  | 458.7  | 418.8  | 371.7  | 324.2  | 69.8  |
| 17.5° | 1160.1 | 1138.1 | 1119.2 | 1087.2 | 1028.4 | 950.7  | 850.7  | 749.2  | 661.6  | 569.7  | 97.3  |
| 20°   | 1738.5 | 1718.9 | 1675.9 | 1606.1 | 1531.1 | 1415.9 | 1297.0 | 1144.7 | 997.1  | 858.9  | 116.2 |
| 21°   | 1937.6 | 1931.0 | 1860.5 | 1817.6 | 1702.0 | 1592.0 | 1454.8 | 1291.8 | 1125.7 | 962.1  | 119.3 |
| 22°   | 2115.3 | 2076.1 | 2038.3 | 1974.7 | 1859.8 | 1740.2 | 1587.5 | 1415.9 | 1235.8 | 1053.9 | 119.7 |
| 23°   | 2238.4 | 2220.5 | 2184.8 | 2112.9 | 1998.8 | 1858.1 | 1697.2 | 1517.7 | 1327.9 | 1118.9 | 118.6 |
| 24°   | 2374.6 | 2351.9 | 2299.6 | 2215.7 | 2100.5 | 1961.6 | 1778.0 | 1599.9 | 1393.6 | 1173.5 | 115.9 |
| 25°   | 2490.1 | 2454.7 | 2392.8 | 2302.4 | 2176.5 | 2033.1 | 1848.5 | 1652.9 | 1439.3 | 1210.3 | 113.1 |
| 26°   | 2565.1 | 2545.8 | 2466.4 | 2368.0 | 2233.3 | 2085.4 | 1897.0 | 1693.4 | 1468.9 | 1227.2 | 108.7 |
| 27°   | 2643.1 | 2607.7 | 2529.7 | 2416.5 | 2270.4 | 2119.4 | 1924.5 | 1713.0 | 1479.2 | 1227.9 | 103.2 |
| 28°   | 2687.8 | 2649.3 | 2560.9 | 2442.0 | 2294.5 | 2138.4 | 1940.3 | 1719.2 | 1477.1 | 1217.2 | 96.6  |
| 29°   | 2701.9 | 2653.4 | 2567.1 | 2446.1 | 2300.3 | 2139.7 | 1937.9 | 1710.3 | 1458.9 | 1191.1 | 89.1  |
| 30°   | 2675.8 | 2626.3 | 2544.4 | 2426.5 | 2281.7 | 2122.5 | 1915.5 | 1680.7 | 1426.6 | 1153.6 | 82.2  |
| 31°   | 2618.7 | 2576.8 | 2497.7 | 2379.4 | 2240.5 | 2082.3 | 1865.0 | 1632.2 | 1371.6 | 1103.4 | 74.3  |
| 32°   | 2543.4 | 2502.1 | 2424.4 | 2317.5 | 2176.2 | 2016.6 | 1795.9 | 1556.6 | 1306.9 | 1028.4 | 66.4  |
| 33°   | 2430.3 | 2406.6 | 2336.8 | 2234.6 | 2093.3 | 1922.8 | 1703.1 | 1466.1 | 1214.8 | 945.2  | 59.5  |
| 34°   | 2315.8 | 2285.9 | 2237.0 | 2125.3 | 1973.3 | 1803.1 | 1582.0 | 1341.3 | 1102.4 | 852.0  | 53.0  |
| 35°   | 2183.7 | 2165.9 | 2089.2 | 1999.8 | 1847.1 | 1673.1 | 1453.4 | 1220.0 | 971.4  | 748.2  | 46.4  |
| 36°   | 2055.8 | 2028.3 | 1941.0 | 1846.4 | 1698.2 | 1510.2 | 1293.2 | 1073.8 | 858.2  | 650.9  | 39.5  |
| 37°   | 1870.2 | 1828.2 | 1766.0 | 1666.3 | 1493.0 | 1332.7 | 1134.7 | 931.1  | 719.0  | 545.7  | 32.0  |
| 38°   | 1651.8 | 1632.2 | 1545.9 | 1445.5 | 1302.1 | 1150.2 | 954.2  | 781.6  | 593.1  | 455.6  | 24.4  |
| 39°   | 1394.3 | 1393.9 | 1311.4 | 1238.9 | 1098.6 | 961.7  | 785.0  | 634.4  | 489.6  | 366.9  | 18.9  |
| 40°   | 1175.9 | 1135.4 | 1084.5 | 993.4  | 885.7  | 769.5  | 614.8  | 496.5  | 379.9  | 295.7  | 14.8  |
| 42.5° | 616.5  | 613.1  | 583.2  | 514.7  | 454.6  | 386.1  | 307.1  | 255.8  | 200.1  | 163.0  | 9.3   |
| 45°   | 264.8  | 266.5  | 245.8  | 235.5  | 212.2  | 183.6  | 155.1  | 129.3  | 110.7  | 89.7   | 5.5   |
| 47.5° | 67.0   | 64.3   | 63.6   | 66.0   | 66.0   | 64.0   | 57.4   | 54.0   | 49.9   | 45.7   | 3.1   |
| 50°   | 28.9   | 28.2   | 27.5   | 27.5   | 25.8   | 24.8   | 23.0   | 21.0   | 19.3   | 17.2   | 1.4   |
| 52.5° | 10.7   | 11.0   | 11.3   | 11.0   | 11.0   | 10.7   | 10.7   | 10.3   | 9.3    | 8.3    | 0.7   |
| 55°   | 3.4    | 3.4    | 3.4    | 3.8    | 3.8    | 4.1    | 4.1    | 4.1    | 4.1    | 3.8    | 0.0   |
| 57.5° | 0.7    | 0.7    | 1.0    | 1.0    | 1.0    | 1.0    | 1.0    | 1.0    | 1.4    | 1.4    | 0.0   |
| 60°   | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.0    | 0.0    | 0.0    | 0.0   |
| 62.5° | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3   |
| 65°   | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3   |
| 67.5° | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3   |
| 70°   | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3   |
| 72.5° | 0.3    | 0.0    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3   |
| 75°   | 0.0    | 0.0    | 0.0    | 0.3    | 0.0    | 0.3    | 0.3    | 0.0    | 0.3    | 0.3    | 0.3   |
| 77.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.3    | 0.3   |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.3   |



TEST NUMBER: P1344087

CATALOG NUMBER: P3A13R209840DE010 E3A301GPH

**CANDELA DISTRIBUTION (continued):**

|       | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 45° |
|-------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 82.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.3 |
| 85°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.3 |
| 87.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.3 |
| 90°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |

TEST NUMBER: P1344087

CATALOG NUMBER: P3A13R209840DE010 E3A301GPH

**CANDELA DISTRIBUTION (continued):**

|       | 67.5° | 90°  | 112.5° | 135° | 157.5° | 180° |
|-------|-------|------|--------|------|--------|------|
| 0°    | 13.1  | 13.1 | 13.1   | 13.1 | 13.1   | 13.1 |
| 2.5°  | 15.1  | 13.4 | 11.3   | 9.6  | 9.3    | 8.9  |
| 5°    | 16.8  | 12.4 | 9.3    | 7.6  | 6.9    | 6.5  |
| 7.5°  | 18.2  | 11.3 | 7.6    | 5.5  | 4.8    | 4.5  |
| 10°   | 18.9  | 10.0 | 6.2    | 4.1  | 3.1    | 3.1  |
| 12.5° | 19.3  | 8.6  | 4.5    | 2.8  | 1.7    | 1.7  |
| 15°   | 18.9  | 7.2  | 3.4    | 1.4  | 0.3    | 0.3  |
| 17.5° | 17.2  | 5.8  | 2.1    | 0.3  | 0.0    | 0.0  |
| 20°   | 14.8  | 4.8  | 1.4    | 0.0  | 0.0    | 0.0  |
| 21°   | 14.1  | 4.1  | 1.0    | 0.0  | 0.0    | 0.0  |
| 22°   | 13.1  | 3.8  | 0.7    | 0.0  | 0.0    | 0.0  |
| 23°   | 12.0  | 3.4  | 0.7    | 0.0  | 0.0    | 0.0  |
| 24°   | 11.0  | 3.1  | 0.3    | 0.0  | 0.0    | 0.0  |
| 25°   | 10.3  | 2.8  | 0.3    | 0.0  | 0.0    | 0.0  |
| 26°   | 9.6   | 2.4  | 0.3    | 0.0  | 0.0    | 0.0  |
| 27°   | 8.6   | 2.1  | 0.0    | 0.0  | 0.0    | 0.0  |
| 28°   | 7.9   | 1.7  | 0.0    | 0.0  | 0.0    | 0.0  |
| 29°   | 6.9   | 1.4  | 0.0    | 0.0  | 0.0    | 0.0  |
| 30°   | 5.8   | 1.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 31°   | 4.8   | 1.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 32°   | 4.1   | 0.7  | 0.0    | 0.0  | 0.0    | 0.0  |
| 33°   | 3.4   | 0.7  | 0.0    | 0.0  | 0.0    | 0.0  |
| 34°   | 3.1   | 0.7  | 0.0    | 0.0  | 0.0    | 0.0  |
| 35°   | 2.8   | 0.7  | 0.0    | 0.0  | 0.0    | 0.0  |
| 36°   | 2.1   | 0.3  | 0.0    | 0.0  | 0.0    | 0.0  |
| 37°   | 1.7   | 0.3  | 0.0    | 0.0  | 0.0    | 0.0  |
| 38°   | 1.4   | 0.3  | 0.0    | 0.0  | 0.0    | 0.0  |
| 39°   | 1.0   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 40°   | 1.0   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 42.5° | 0.3   | 0.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 45°   | 0.0   | 0.3  | 0.0    | 0.0  | 0.3    | 0.3  |
| 47.5° | 0.0   | 0.3  | 0.0    | 0.0  | 0.3    | 0.7  |
| 50°   | 0.0   | 0.3  | 0.3    | 0.3  | 0.7    | 1.0  |
| 52.5° | 0.0   | 0.7  | 0.3    | 0.3  | 1.0    | 1.0  |
| 55°   | 0.3   | 0.7  | 0.3    | 0.7  | 1.4    | 1.4  |
| 57.5° | 0.3   | 0.7  | 0.7    | 1.0  | 1.4    | 1.7  |
| 60°   | 0.7   | 1.0  | 1.0    | 1.0  | 1.7    | 1.7  |
| 62.5° | 0.7   | 1.0  | 1.4    | 1.4  | 1.7    | 2.1  |
| 65°   | 0.7   | 1.4  | 1.4    | 1.4  | 1.7    | 2.1  |
| 67.5° | 1.0   | 1.4  | 1.4    | 1.4  | 1.7    | 2.1  |
| 70°   | 1.0   | 1.4  | 1.4    | 1.4  | 1.7    | 1.7  |
| 72.5° | 1.0   | 1.4  | 1.0    | 1.4  | 1.4    | 1.7  |
| 75°   | 1.0   | 1.4  | 1.0    | 1.0  | 1.4    | 1.4  |
| 77.5° | 0.7   | 1.0  | 1.0    | 0.7  | 1.0    | 1.0  |
| 80°   | 0.7   | 1.0  | 0.7    | 0.7  | 1.0    | 1.0  |



TEST NUMBER: P1344087

CATALOG NUMBER: P3A13R209840DE010 E3A301GPH

**CANDELA DISTRIBUTION (continued):**

|       | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° |
|-------|-------|-----|--------|------|--------|------|
| 82.5° | 0.7   | 1.0 | 0.7    | 0.3  | 0.7    | 0.7  |
| 85°   | 0.7   | 1.0 | 0.7    | 0.3  | 0.3    | 0.3  |
| 87.5° | 0.7   | 1.0 | 0.7    | 0.3  | 0.0    | 0.3  |
| 90°   | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |

(END OF REPORT)