

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426633

Luminaire Tested: P3A13RHB2750DE010 E3HY1MW_2700K

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426633
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13RHB2750DE010 E3HY1MW_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, RH optic, 2700K CCT AND, 90CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 368.0 lumens
Efficiency: N/A
Efficacy: 19.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426633

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1MW_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1426633

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	96	96	94
2	108	104	100	97	106	102	98	96	99	96	93	96	93	91	93	91	90	90	90	88
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	84	84	82
4	99	91	86	82	97	90	86	82	88	84	81	86	83	80	84	81	79	79	79	78
5	94	86	81	77	93	85	80	77	84	79	76	82	78	75	81	77	75	75	75	73
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	73	71	71	71	69
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	67	67	66
8	83	74	68	65	82	73	68	65	72	68	64	71	67	64	70	67	64	64	64	63
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	61	61	60
10	76	68	62	59	75	67	62	59	66	62	59	66	61	58	65	61	58	58	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	177464
5°	162579
10°	142082
15°	124632
20°	63075
25°	31405
30°	28384
35°	21576
40°	15171
45°	10234
50°	6550
55°	4396
60°	3026
65°	2387
70°	1475
75°	1271
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10234 cd/sqm

TEST NUMBER: P1426633

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.2	18.3
10°-20°	139.1	37.8
20°-30°	67.8	18.4
30°-40°	50.7	13.8
40°-50°	26.1	7.1
50°-60°	10.7	2.9
60°-70°	4.4	1.2
70°-80°	1.6	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	274.2	74.5
0°-40°	324.9	88.3
0°-60°	361.7	98.3
0°-90°	368.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	368.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	809	
5°	739	67
15°	549	139
25°	130	68
35°	81	51
45°	33	26
55°	12	11
65°	5	4
75°	2	2
85°	0	0
90°	0	

TEST NUMBER: P1426633

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	809.3
2.5°	790.8
5°	738.6
7.5°	682.6
10°	638.1
12.5°	605.0
15°	549.0
17.5°	428.4
20°	270.3
22.5°	160.5
25°	129.8
27.5°	119.8
30°	112.1
32.5°	98.3
35°	80.6
37.5°	66.0
40°	53.0
42.5°	42.2
45°	33.0
47.5°	25.3
50°	19.2
52.5°	14.6
55°	11.5
57.5°	9.2
60°	6.9
62.5°	5.4
65°	4.6
67.5°	3.1
70°	2.3
72.5°	2.3
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)