

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426635

Luminaire Tested: P3A13RHB2750DE010 E3HY1MW_3500K

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426635
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13RHB2750DE010 E3HY1MW_3500K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, RH optic, 3500K CCT AND, 80CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 372.0 lumens
Efficiency: N/A
Efficacy: 19.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426635

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1MW_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1426635

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1MW_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	98	96	99	96	93		96	93	91		93
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89
4	99	91	86	82	97	90	86	82	88	84	81		86	83	80		84
5	94	86	81	77	93	85	80	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	68	62	59	75	67	62	59	66	62	59		66	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	179394
5°	164362
10°	143618
15°	125994
20°	63752
25°	31744
30°	28688
35°	21817
40°	15343
45°	10358
50°	6618
55°	4435
60°	3070
65°	2439
70°	1475
75°	1356
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 10358 cd/sqm

TEST NUMBER: P1426635

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.0	18.3
10°-20°	140.6	37.8
20°-30°	68.6	18.4
30°-40°	51.2	13.8
40°-50°	26.4	7.1
50°-60°	10.8	2.9
60°-70°	4.4	1.2
70°-80°	1.6	0.4
80°-90°	0.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	277.2	74.5
0°-40°	328.4	88.3
0°-60°	365.6	98.3
0°-90°	372.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	372.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	818	
5°	747	68
15°	555	141
25°	131	69
35°	82	51
45°	33	26
55°	12	11
65°	5	4
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1426635

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1MW_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	818.1
2.5°	799.4
5°	746.7
7.5°	690.0
10°	645.0
12.5°	611.6
15°	555.0
17.5°	433.1
20°	273.2
22.5°	162.2
25°	131.2
27.5°	121.1
30°	113.3
32.5°	99.3
35°	81.5
37.5°	66.7
40°	53.6
42.5°	42.7
45°	33.4
47.5°	25.6
50°	19.4
52.5°	14.7
55°	11.6
57.5°	9.3
60°	7.0
62.5°	5.4
65°	4.7
67.5°	3.1
70°	2.3
72.5°	2.3
75°	1.6
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)