

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426642

Luminaire Tested: P3A13RHB2750DE010 E3HY1WMH_5000K

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426642
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13RHB2750DE010 E3HY1WMH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, RH optic, 5000K CCT AND, 80CRI , E3HY1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 502.0 lumens
Efficiency: N/A
Efficacy: 26.3 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426642

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1WMH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1426642

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99
2	109	105	102	99	107	104	100	98	100	98	96		97	95	93		95
3	105	99	95	92	103	98	94	91	95	92	89		93	90	88		91
4	101	94	89	86	99	93	89	85	91	87	84		89	86	83		87
5	96	89	84	81	95	88	84	80	87	83	79		85	82	79		84
6	93	85	80	76	91	84	79	76	83	78	75		81	78	75		80
7	89	81	76	72	88	80	75	72	79	75	72		78	74	71		77
8	85	77	72	69	84	77	72	68	76	71	68		75	71	68		74
9	82	74	69	65	81	73	69	65	73	68	65		72	68	65		71
10	79	71	66	62	78	70	66	62	70	65	62		69	65	62		68

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	250923
5°	227470
10°	196990
15°	179025
20°	99875
25°	62012
30°	49704
35°	27037
40°	13626
45°	6109
50°	1979
55°	306
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 6109 cd/sqm

TEST NUMBER: P1426642

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	93.7	18.7
10°-20°	199.9	39.8
20°-30°	123.0	24.5
30°-40°	67.1	13.4
40°-50°	16.8	3.3
50°-60°	1.5	0.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	416.6	83.0
0°-40°	483.7	96.3
0°-60°	502.0	100.0
0°-90°	502.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	502.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1144	
5°	1033	94
15°	789	200
25°	256	123
35°	101	67
45°	20	17
55°	1	2
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426642

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1144.3
2.5°	1115.5
5°	1033.4
7.5°	946.3
10°	884.7
12.5°	837.9
15°	788.6
17.5°	627.6
20°	428.0
22.5°	286.7
25°	256.3
27.5°	229.2
30°	196.3
32.5°	147.0
35°	101.0
37.5°	69.0
40°	47.6
42.5°	32.0
45°	19.7
47.5°	10.7
50°	5.8
52.5°	2.5
55°	0.8
57.5°	0.8
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)