

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426119

Luminaire Tested: P3A02RHB2750DE010 E3HY1LI_3000K

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426119
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-1)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02RHB2750DE010 E3HY1LI_3000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, RH optic, 3000K CCT AND, 90CRI , E3HY1LI TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 152.0 lumens
Efficiency: N/A
Efficacy: 52.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426119

CATALOG NUMBER: P3A02RHB2750DE010 E3HY1LI_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1426119

CATALOG NUMBER: P3A02RHB2750DE010 E3HY1LI_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104		103	102	101		100	99	98	97
2	111	108	105	102	109	106	103	101	103	101	99		100	98	97		98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95		97	95	93		95	93	92	91
4	105	99	95	92	103	98	95	92	96	93	91		94	92	90		93	91	89	88
5	102	96	92	89	100	95	91	88	93	90	88		92	89	87		90	88	86	85
6	99	92	88	85	97	92	88	85	90	87	85		89	86	84		88	86	84	82
7	96	89	85	82	95	89	85	82	88	84	82		87	84	81		86	83	81	80
8	93	87	83	80	92	86	82	80	85	82	79		84	81	79		84	81	79	78
9	91	84	80	77	90	84	80	77	83	79	77		82	79	77		81	79	77	76
10	88	82	78	75	87	81	77	75	81	77	75		80	77	75		79	76	74	73

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	106943
5°	103500
10°	94454
15°	80727
20°	31666
25°	7234
30°	3266
35°	402
40°	0
45°	0
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 0 cd/sqm

TEST NUMBER: P1426119

CATALOG NUMBER: P3A02RHB2750DE010 E3HY1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.2	28.4
10°-20°	87.6	57.6
20°-30°	19.1	12.5
30°-40°	2.1	1.4
40°-50°	0.0	0.0
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	149.9	98.6
0°-40°	152.0	100.0
0°-60°	152.0	100.0
0°-90°	152.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	152.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	488	
5°	470	43
15°	356	88
25°	30	19
35°	2	2
45°	0	0
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426119

CATALOG NUMBER: P3A02RHB2750DE010 E3HY1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	487.7
2.5°	490.3
5°	470.2
7.5°	442.8
10°	424.2
12.5°	401.0
15°	355.6
17.5°	258.1
20°	135.7
22.5°	52.1
25°	29.9
27.5°	20.1
30°	12.9
32.5°	5.7
35°	1.5
37.5°	0.5
40°	0.0
42.5°	0.0
45°	0.0
47.5°	0.0
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)