

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426621

Luminaire Tested: P3A13RHB2750DE010 E3HY1GPH_4000K

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426621
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-6)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13RHB2750DE010 E3HY1GPH_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, RH optic, 4000K CCT AND, 80CRI , E3HY1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 275.0 lumens
Efficiency: N/A
Efficacy: 14.4 lumens/watt
Spacing Criteria (0/90/45): 0.59 / 0.59 / 0.51
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426621

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1GPH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1426621

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1GPH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20				20				20
RC	80				70				50				30				10				0				0				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100											
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96											
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	92											
3	107	102	98	95	105	101	97	95	98	95	93	96	94	92	94	92	90	89											
4	103	98	94	90	102	97	93	90	95	91	89	93	90	88	91	89	87	86											
5	100	94	89	86	99	93	89	86	91	88	85	90	87	84	88	86	84	83											
6	97	90	86	83	96	89	85	82	88	84	82	87	84	81	86	83	81	80											
7	94	87	82	79	93	86	82	79	85	81	79	84	81	78	83	80	78	77											
8	91	84	79	76	90	83	79	76	82	79	76	81	78	76	81	78	75	74											
9	88	81	77	74	87	81	76	74	80	76	73	79	76	73	78	75	73	72											
10	85	78	74	71	85	78	74	71	77	73	71	77	73	71	76	73	71	70											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	186717
5°	170460
10°	147693
15°	129921
20°	56518
25°	21654
30°	14635
35°	4952
40°	1546
45°	465
50°	0
55°	0
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 465 cd/sqm

TEST NUMBER: P1426621

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1GPH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.2	25.5
10°-20°	140.9	51.2
20°-30°	47.8	17.4
30°-40°	14.6	5.3
40°-50°	1.5	0.6
50°-60°	0.0	0.0
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	258.9	94.1
0°-40°	273.5	99.4
0°-60°	275.0	100.0
0°-90°	275.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	275.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	852	
5°	774	70
15°	572	141
25°	90	48
35°	18	15
45°	2	2
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426621

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1GPH_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	851.5
2.5°	833.0
5°	774.4
7.5°	709.6
10°	663.3
12.5°	621.6
15°	572.3
17.5°	425.0
20°	242.2
22.5°	118.0
25°	89.5
27.5°	72.5
30°	57.8
32.5°	37.0
35°	18.5
37.5°	10.0
40°	5.4
42.5°	3.1
45°	1.5
47.5°	0.8
50°	0.0
52.5°	0.0
55°	0.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)