

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426638

Luminaire Tested: P3A13RHB2750DE010 E3HY1WMH\_2700K

Issue Date: 3/9/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1426638  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13RHB2750DE010 E3HY1WMH\_2700K  
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, RH optic, 2700K CCT AND, 90CRI , E3HY1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 469.0 lumens  
Efficiency: N/A  
Efficacy: 24.6 lumens/watt  
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1426638

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1WMH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1426638

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1WMH\_2700K

### COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |  |     |  |  |   |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|--|--|---|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |  |     |  |  |   |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |  |     |  |  | 0 |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 0   |  |  |   |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |  |     |  |  |   |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |  | 100 |  |  |   |
| 1   | 114 | 112 | 110 | 108 |  | 112 | 110 | 108 | 106 |  | 106 | 104 | 103 |  | 102 | 101 | 100 |  | 99  | 98  | 97  |  | 95  |  |  |   |
| 2   | 109 | 105 | 102 | 99  |  | 107 | 104 | 100 | 98  |  | 100 | 98  | 96  |  | 97  | 95  | 93  |  | 95  | 93  | 92  |  | 90  |  |  |   |
| 3   | 105 | 99  | 95  | 92  |  | 103 | 98  | 94  | 91  |  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  | 89  | 87  |  | 85  |  |  |   |
| 4   | 101 | 94  | 89  | 86  |  | 99  | 93  | 89  | 85  |  | 91  | 87  | 84  |  | 89  | 86  | 83  |  | 87  | 84  | 82  |  | 81  |  |  |   |
| 5   | 96  | 89  | 84  | 81  |  | 95  | 88  | 84  | 80  |  | 87  | 83  | 79  |  | 85  | 82  | 79  |  | 84  | 81  | 78  |  | 77  |  |  |   |
| 6   | 93  | 85  | 80  | 76  |  | 91  | 84  | 79  | 76  |  | 83  | 78  | 75  |  | 81  | 78  | 75  |  | 80  | 77  | 74  |  | 73  |  |  |   |
| 7   | 89  | 81  | 76  | 72  |  | 88  | 80  | 75  | 72  |  | 79  | 75  | 72  |  | 78  | 74  | 71  |  | 77  | 73  | 71  |  | 70  |  |  |   |
| 8   | 85  | 77  | 72  | 69  |  | 84  | 77  | 72  | 68  |  | 76  | 71  | 68  |  | 75  | 71  | 68  |  | 74  | 70  | 68  |  | 66  |  |  |   |
| 9   | 82  | 74  | 69  | 65  |  | 81  | 73  | 69  | 65  |  | 73  | 68  | 65  |  | 72  | 68  | 65  |  | 71  | 67  | 65  |  | 64  |  |  |   |
| 10  | 79  | 71  | 66  | 62  |  | 78  | 70  | 66  | 62  |  | 70  | 65  | 62  |  | 69  | 65  | 62  |  | 68  | 65  | 62  |  | 61  |  |  |   |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 234411 |
| 5°  | 212502 |
| 10° | 184031 |
| 15° | 167243 |
| 20° | 93295  |
| 25° | 57923  |
| 30° | 46438  |
| 35° | 25270  |
| 40° | 12738  |
| 45° | 5706   |
| 50° | 1842   |
| 55° | 306    |
| 60° | 0      |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle:  $45^\circ$

Luminance: 5706 cd/sqm

TEST NUMBER: P1426638

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1WMH\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 87.6   | 18.7      |
| 10°-20°   | 186.7  | 39.8      |
| 20°-30°   | 114.9  | 24.5      |
| 30°-40°   | 62.7   | 13.4      |
| 40°-50°   | 15.7   | 3.3       |
| 50°-60°   | 1.4    | 0.3       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 389.2  | 83.0      |
| 0°-40°    | 451.9  | 96.3      |
| 0°-60°    | 469.0  | 100.0     |
| 0°-90°    | 469.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 469.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1069 |      |
| 5°  | 965  | 88   |
| 15° | 737  | 187  |
| 25° | 239  | 115  |
| 35° | 94   | 63   |
| 45° | 18   | 16   |
| 55° | 1    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1426638

CATALOG NUMBER: P3A13RHB2750DE010 E3HY1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1069.0 |
| 2.5°  | 1042.2 |
| 5°    | 965.4  |
| 7.5°  | 884.1  |
| 10°   | 826.5  |
| 12.5° | 782.8  |
| 15°   | 736.7  |
| 17.5° | 586.3  |
| 20°   | 399.8  |
| 22.5° | 267.8  |
| 25°   | 239.4  |
| 27.5° | 214.1  |
| 30°   | 183.4  |
| 32.5° | 137.4  |
| 35°   | 94.4   |
| 37.5° | 64.5   |
| 40°   | 44.5   |
| 42.5° | 29.9   |
| 45°   | 18.4   |
| 47.5° | 10.0   |
| 50°   | 5.4    |
| 52.5° | 2.3    |
| 55°   | 0.8    |
| 57.5° | 0.8    |
| 60°   | 0.0    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)