

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426725

Luminaire Tested: P3A17RH9030D2WDE010 E3HY1MW

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426725
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A17RH9030D2WDE010 E3HY1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, RH optic, 3000K CCT AND, 90CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 691.0 lumens
Efficiency: N/A
Efficacy: 25.3 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 27.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426725

CATALOG NUMBER: P3A17RH9030D2WDE010 E3HY1MW

Luminous Intensity Polar Plot



TEST NUMBER: P1426725

CATALOG NUMBER: P3A17RH9030D2WDE010 E3HY1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98
2	108	104	100	97	106	102	98	96	99	96	93		96	93	91		93
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89
4	99	91	86	82	97	90	86	82	88	84	81		86	83	80		84
5	94	86	81	77	93	85	80	77	84	79	76		82	78	75		81
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68
10	76	68	62	59	75	67	62	59	66	62	59		66	61	58		65

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	333219
5°	305282
10°	266773
15°	234008
20°	118427
25°	58963
30°	53299
35°	40529
40°	28482
45°	19227
50°	12281
55°	8258
60°	5701
65°	4514
70°	2757
75°	2457
80°	1768
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 19227 cd/sqm

TEST NUMBER: P1426725

CATALOG NUMBER: P3A17RH9030D2WDE010 E3HY1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	126.3	18.3
10°-20°	261.2	37.8
20°-30°	127.4	18.4
30°-40°	95.2	13.8
40°-50°	49.0	7.1
50°-60°	20.2	2.9
60°-70°	8.2	1.2
70°-80°	3.0	0.4
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	514.8	74.5
0°-40°	610.0	88.3
0°-60°	679.2	98.3
0°-90°	691.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	691.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1520	
5°	1387	126
15°	1031	261
25°	244	127
35°	151	95
45°	62	49
55°	22	20
65°	9	8
75°	3	3
85°	0	1
90°	0	

TEST NUMBER: P1426725

CATALOG NUMBER: P3A17RH9030D2WDE010 E3HY1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1519.6
2.5°	1485.0
5°	1386.9
7.5°	1281.7
10°	1198.1
12.5°	1136.1
15°	1030.8
17.5°	804.5
20°	507.5
22.5°	301.3
25°	243.7
27.5°	224.9
30°	210.5
32.5°	184.5
35°	151.4
37.5°	124.0
40°	99.5
42.5°	79.3
45°	62.0
47.5°	47.6
50°	36.0
52.5°	27.4
55°	21.6
57.5°	17.3
60°	13.0
62.5°	10.1
65°	8.7
67.5°	5.8
70°	4.3
72.5°	4.3
75°	2.9
77.5°	1.4
80°	1.4
82.5°	1.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)