

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426149

Luminaire Tested: P3A05RH9030D2WDE010 E3HY1MW

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426149
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A05RH9030D2WDE010 E3HY1MW
Description: 3in Adjustable Dim to Warm LED luminaire with, RH optic, 3000K CCT AND, 90CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 240.0 lumens
Efficiency: N/A
Efficacy: 21.6 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426149

CATALOG NUMBER: P3A05RH9030D2WDE010 E3HY1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1426149

CATALOG NUMBER: P3A05RH9030D2WDE010 E3HY1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	102		101	100	99		98	97	96	94
2	108	104	100	97	106	102	98	96	99	96	93		96	93	91		93	91	90	88
3	103	97	93	89	101	96	92	88	93	90	87		91	88	85		89	86	84	82
4	99	91	86	82	97	90	86	82	88	84	81		86	83	80		84	81	79	78
5	94	86	81	77	93	85	80	77	84	79	76		82	78	75		81	77	75	73
6	90	82	76	72	89	81	76	72	80	75	72		78	74	71		77	73	71	69
7	86	78	72	68	85	77	72	68	76	71	68		75	70	67		74	70	67	66
8	83	74	68	65	82	73	68	65	72	68	64		71	67	64		70	67	64	63
9	79	71	65	62	78	70	65	61	69	65	61		68	64	61		68	64	61	60
10	76	68	62	59	75	67	62	59	66	62	59		66	61	58		65	61	58	57

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	115736
5°	106031
10°	92650
15°	81272
20°	41140
25°	20469
30°	18509
35°	14081
40°	9904
45°	6667
50°	4264
55°	2867
60°	1974
65°	1557
70°	962
75°	847
80°	631
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6667 cd/sqm

TEST NUMBER: P1426149

CATALOG NUMBER: P3A05RH9030D2WDE010 E3HY1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.9	18.3
10°-20°	90.7	37.8
20°-30°	44.2	18.4
30°-40°	33.1	13.8
40°-50°	17.0	7.1
50°-60°	7.0	2.9
60°-70°	2.8	1.2
70°-80°	1.1	0.4
80°-90°	0.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	178.8	74.5
0°-40°	211.9	88.3
0°-60°	235.9	98.3
0°-90°	240.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	240.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	528	
5°	482	44
15°	358	91
25°	85	44
35°	53	33
45°	22	17
55°	8	7
65°	3	3
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1426149

CATALOG NUMBER: P3A05RH9030D2WDE010 E3HY1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	527.8
2.5°	515.8
5°	481.7
7.5°	445.2
10°	416.1
12.5°	394.6
15°	358.0
17.5°	279.4
20°	176.3
22.5°	104.7
25°	84.6
27.5°	78.1
30°	73.1
32.5°	64.1
35°	52.6
37.5°	43.1
40°	34.6
42.5°	27.5
45°	21.5
47.5°	16.5
50°	12.5
52.5°	9.5
55°	7.5
57.5°	6.0
60°	4.5
62.5°	3.5
65°	3.0
67.5°	2.0
70°	1.5
72.5°	1.5
75°	1.0
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)