

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426126

Luminaire Tested: P3A02RHB2750DE010 E3HY1MW_4000K

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426126
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-3)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02RHB2750DE010 E3HY1MW_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, RH optic, 4000K CCT AND, 80CRI , E3HY1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 97.0 lumens
Efficiency: N/A
Efficacy: 33.4 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.53
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426126

CATALOG NUMBER: P3A02RHB2750DE010 E3HY1MW_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1426126

CATALOG NUMBER: P3A02RHB2750DE010 E3HY1MW_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	102	101	100	99	98	97	96	94		
2	108	104	100	97	106	102	99	96	99	96	93	96	94	91	93	91	90	88		
3	103	97	93	89	101	96	92	88	93	90	87	91	88	85	89	86	84	82		
4	99	92	86	82	97	90	86	82	88	84	81	86	83	80	84	81	79	78		
5	94	86	81	77	93	85	80	77	84	79	76	82	78	75	81	77	75	73		
6	90	82	76	72	89	81	76	72	80	75	72	78	74	71	77	73	71	69		
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66		
8	83	74	68	65	82	73	68	65	72	68	64	71	67	64	70	67	64	63		
9	79	71	65	62	78	70	65	61	69	65	61	68	64	61	68	64	61	60		
10	76	68	62	59	75	67	62	59	66	62	59	66	61	58	65	61	58	57		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	46773
5°	42857
10°	37452
15°	32849
20°	16615
25°	8275
30°	7470
35°	5702
40°	4008
45°	2698
50°	1740
55°	1147
60°	789
65°	623
70°	385
75°	339
80°	253
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2698 cd/sqm

TEST NUMBER: P1426126

CATALOG NUMBER: P3A02RHB2750DE010 E3HY1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	17.7	18.3
10°-20°	36.7	37.8
20°-30°	17.9	18.4
30°-40°	13.4	13.8
40°-50°	6.9	7.1
50°-60°	2.8	2.9
60°-70°	1.1	1.2
70°-80°	0.4	0.4
80°-90°	0.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	72.3	74.5
0°-40°	85.6	88.3
0°-60°	95.3	98.3
0°-90°	97.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	97.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	213	
5°	195	18
15°	145	37
25°	34	18
35°	21	13
45°	9	7
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P1426126

CATALOG NUMBER: P3A02RHB2750DE010 E3HY1MW_4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	213.3
2.5°	208.5
5°	194.7
7.5°	179.9
10°	168.2
12.5°	159.5
15°	144.7
17.5°	112.9
20°	71.2
22.5°	42.3
25°	34.2
27.5°	31.6
30°	29.5
32.5°	25.9
35°	21.3
37.5°	17.4
40°	14.0
42.5°	11.1
45°	8.7
47.5°	6.7
50°	5.1
52.5°	3.8
55°	3.0
57.5°	2.4
60°	1.8
62.5°	1.4
65°	1.2
67.5°	0.8
70°	0.6
72.5°	0.6
75°	0.4
77.5°	0.2
80°	0.2
82.5°	0.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)