

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426128

Luminaire Tested: P3A02RHB2750DE010 E3HY1WMH_2700K

Issue Date: 3/9/2026

Test Information

Test Method: LM-79-2019
Report Number: P1426128
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/9/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A02RHB2750DE010 E3HY1WMH_2700K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, RH optic, 2700K CCT AND, 90CRI , E3HY1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 123.0 lumens
Efficiency: N/A
Efficacy: 42.4 lumens/watt
Spacing Criteria (0/90/45): 0.61 / 0.61 / 0.55
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 2.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1426128

CATALOG NUMBER: P3A02RHB2750DE010 E3HY1WMH_2700K

Luminous Intensity Polar Plot



TEST NUMBER: P1426128

CATALOG NUMBER: P3A02RHB2750DE010 E3HY1WMH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	99	99
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95	94	93
2	109	105	102	99	107	104	100	98	100	98	96	97	95	93	95	93	92	90	89	88
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85	84	83
4	101	94	89	86	99	93	89	85	91	87	84	89	86	83	87	84	82	81	80	79
5	96	89	84	81	95	88	84	80	87	83	79	85	82	79	84	81	78	77	76	75
6	93	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73	72	71
7	89	81	76	72	88	80	75	72	79	75	72	78	74	71	77	73	71	70	69	68
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	66	65	64
9	82	74	69	65	81	73	69	65	73	68	65	72	68	65	71	67	65	64	63	62
10	79	71	66	62	78	70	66	62	70	65	62	69	65	62	68	65	62	61	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	61486
5°	55734
10°	48273
15°	43860
20°	24479
25°	15194
30°	12179
35°	6639
40°	3349
45°	1489
50°	478
55°	76
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1489 cd/sqm

TEST NUMBER: P1426128

CATALOG NUMBER: P3A02RHB2750DE010 E3HY1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.0	18.7
10°-20°	49.0	39.8
20°-30°	30.1	24.5
30°-40°	16.4	13.4
40°-50°	4.1	3.3
50°-60°	0.4	0.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	102.1	83.0
0°-40°	118.5	96.4
0°-60°	123.0	100.0
0°-90°	123.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	123.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	280	
5°	253	23
15°	193	49
25°	63	30
35°	25	16
45°	5	4
55°	0	0
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1426128

CATALOG NUMBER: P3A02RHB2750DE010 E3HY1WMH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	280.4
2.5°	273.3
5°	253.2
7.5°	231.9
10°	216.8
12.5°	205.3
15°	193.2
17.5°	153.8
20°	104.9
22.5°	70.2
25°	62.8
27.5°	56.2
30°	48.1
32.5°	36.0
35°	24.8
37.5°	16.9
40°	11.7
42.5°	7.8
45°	4.8
47.5°	2.6
50°	1.4
52.5°	0.6
55°	0.2
57.5°	0.2
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)