

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295373

Luminaire Tested: P3A13R15W2N902750DE010 E3DL1LI\_3000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1295373  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-3)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R15W2N902750DE010 E3DL1LI\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,  
E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 793.0 lumens  
Efficiency: N/A  
Efficacy: 64.5 lumens/watt  
Spacing Criteria (0/90/45): 0.4 / 0.4 / 0.43  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1295373

CATALOG NUMBER: P3A13R15W2N902750DE010 E3DL1LI\_3000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1295373

CATALOG NUMBER: P3A13R15W2N902750DE010 E3DL1LI\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |    |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |    |    | 0  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 | 0  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |    |
| 1   | 114 | 112 | 110 | 108 | 112 | 110 | 108 | 106 | 106 | 104 | 103 | 102 | 101 | 100 | 99  | 98  | 97  | 95  |    |    |    |
| 2   | 110 | 106 | 103 | 100 | 108 | 104 | 101 | 99  | 101 | 99  | 97  | 98  | 96  | 95  | 96  | 94  | 93  | 91  |    |    |    |
| 3   | 106 | 101 | 97  | 93  | 104 | 99  | 96  | 93  | 97  | 94  | 91  | 94  | 92  | 90  | 92  | 90  | 88  | 87  |    |    |    |
| 4   | 102 | 96  | 92  | 88  | 100 | 95  | 91  | 88  | 93  | 89  | 87  | 91  | 88  | 86  | 89  | 87  | 85  | 83  |    |    |    |
| 5   | 98  | 92  | 87  | 84  | 97  | 91  | 87  | 83  | 89  | 85  | 83  | 88  | 84  | 82  | 86  | 83  | 81  | 80  |    |    |    |
| 6   | 95  | 88  | 83  | 80  | 94  | 87  | 83  | 80  | 86  | 82  | 79  | 85  | 81  | 79  | 83  | 80  | 78  | 77  |    |    |    |
| 7   | 92  | 85  | 80  | 77  | 91  | 84  | 80  | 76  | 83  | 79  | 76  | 82  | 78  | 76  | 81  | 78  | 75  | 74  |    |    |    |
| 8   | 89  | 81  | 77  | 74  | 88  | 81  | 77  | 73  | 80  | 76  | 73  | 79  | 75  | 73  | 78  | 75  | 73  | 72  |    |    |    |
| 9   | 86  | 79  | 74  | 71  | 85  | 78  | 74  | 71  | 77  | 73  | 71  | 77  | 73  | 70  | 76  | 73  | 70  | 69  |    |    |    |
| 10  | 84  | 76  | 71  | 68  | 83  | 76  | 71  | 68  | 75  | 71  | 68  | 74  | 71  | 68  | 74  | 70  | 68  | 67  |    |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 677424 |
| 5°  | 601319 |
| 10° | 417583 |
| 15° | 246948 |
| 20° | 140642 |
| 25° | 80400  |
| 30° | 44488  |
| 35° | 23718  |
| 40° | 13110  |
| 45° | 7102   |
| 50° | 4435   |
| 55° | 3517   |
| 60° | 3026   |
| 65° | 2750   |
| 70° | 2436   |
| 75° | 2626   |
| 80° | 1894   |
| 85° | 2013   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 7102 cd/sqm

TEST NUMBER: P1295373

CATALOG NUMBER: P3A13R15W2N902750DE010 E3DL1LI\_3000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 232.3  | 29.3      |
| 10°-20°   | 306.6  | 38.7      |
| 20°-30°   | 157.9  | 19.9      |
| 30°-40°   | 59.3   | 7.5       |
| 40°-50°   | 19.4   | 2.4       |
| 50°-60°   | 8.3    | 1.1       |
| 60°-70°   | 5.3    | 0.7       |
| 70°-80°   | 3.1    | 0.4       |
| 80°-90°   | 0.8    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 696.7  | 87.9      |
| 0°-40°    | 756.0  | 95.3      |
| 0°-60°    | 783.7  | 98.8      |
| 0°-90°    | 793.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 793.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3089 |      |
| 5°  | 2732 | 232  |
| 15° | 1088 | 307  |
| 25° | 332  | 158  |
| 35° | 89   | 59   |
| 45° | 23   | 19   |
| 55° | 9    | 8    |
| 65° | 5    | 5    |
| 75° | 3    | 3    |
| 85° | 1    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1295373

CATALOG NUMBER: P3A13R15W2N902750DE010 E3DL1LI\_3000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3089.3 |
| 1°    | 3083.2 |
| 2°    | 3042.7 |
| 3°    | 2965.6 |
| 4°    | 2864.0 |
| 5°    | 2731.8 |
| 6°    | 2582.1 |
| 7°    | 2417.8 |
| 8°    | 2235.3 |
| 9°    | 2055.0 |
| 10°   | 1875.4 |
| 12.5° | 1443.1 |
| 15°   | 1087.8 |
| 17.5° | 814.3  |
| 20°   | 602.7  |
| 22.5° | 450.0  |
| 25°   | 332.3  |
| 27.5° | 242.2  |
| 30°   | 175.7  |
| 32.5° | 124.5  |
| 35°   | 88.6   |
| 37.5° | 63.4   |
| 40°   | 45.8   |
| 42.5° | 32.8   |
| 45°   | 22.9   |
| 47.5° | 16.8   |
| 50°   | 13.0   |
| 52.5° | 10.7   |
| 55°   | 9.2    |
| 57.5° | 7.6    |
| 60°   | 6.9    |
| 62.5° | 6.1    |
| 65°   | 5.3    |
| 67.5° | 4.6    |
| 70°   | 3.8    |
| 72.5° | 3.8    |
| 75°   | 3.1    |
| 77.5° | 2.3    |
| 80°   | 1.5    |
| 82.5° | 1.5    |
| 85°   | 0.8    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)