

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295649

Luminaire Tested: P3A13R15W2N902765DE010 E3PHLD1MW_3500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295649
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R15W2N902765DE010 E3PHLD1MW_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3500K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 511.0 lumens
Efficiency: N/A
Efficacy: 41.5 lumens/watt
Spacing Criteria (0/90/45): 0.56 / 0.56 / 0.66
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295649

CATALOG NUMBER: P3A13R15W2N902765DE010 E3PHLD1MW_3500K

Luminous Intensity Polar Plot



CATALOG NUMBER: P3A13R15W2N902765DE010 E3PHLD1MW_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	112	108	105	102		109	106	103	101		102	100	97		98	96	95		95	93	92		90			
2	104	98	93	89		102	97	92	88		93	89	86		90	87	84		87	85	82		80			
3	98	90	84	79		96	88	83	78		85	81	77		83	79	75		81	77	74		72			
4	92	82	76	70		90	81	75	70		79	73	69		77	72	68		75	71	67		66			
5	86	76	69	64		84	75	68	63		73	67	63		71	66	62		70	65	62		60			
6	81	71	63	58		79	70	63	58		68	62	58		67	61	57		65	60	57		55			
7	77	66	59	54		75	65	58	54		64	58	53		62	57	53		61	56	53		51			
8	72	61	55	50		71	61	54	50		60	54	49		59	53	49		58	53	49		47			
9	69	58	51	47		68	57	51	46		56	50	46		55	50	46		54	49	46		44			
10	65	54	48	44		64	54	48	44		53	47	43		52	47	43		52	47	43		42			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	148694
5°	139401
10°	114315
15°	88809
20°	70099
25°	55866
30°	44842
35°	36594
40°	30171
45°	25367
50°	21799
55°	18848
60°	16709
65°	14528
70°	12951
75°	10421
80°	8461
85°	5535

MAXIMUM LUMINANCE 45°-90°:

Luminance: 25367 cd/sqm

TEST NUMBER: P1295649

CATALOG NUMBER: P3A13R15W2N902765DE010 E3PHLD1MW_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.6	11.1
10°-20°	109.6	21.4
20°-30°	106.5	20.8
30°-40°	86.1	16.8
40°-50°	63.9	12.5
50°-60°	44.6	8.7
60°-70°	28.0	5.5
70°-80°	13.3	2.6
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	272.7	53.4
0°-40°	358.7	70.2
0°-60°	467.3	91.4
0°-90°	511.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	511.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	678	
5°	633	57
15°	391	110
25°	231	107
35°	137	86
45°	82	64
55°	49	45
65°	28	28
75°	12	13
85°	2	2
90°	0	

TEST NUMBER: P1295649

CATALOG NUMBER: P3A13R15W2N902765DE010 E3PHLD1MW_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	678.1
2.5°	666.9
5°	633.3
7.5°	579.5
10°	513.4
12.5°	448.4
15°	391.2
17.5°	343.0
20°	300.4
22.5°	263.4
25°	230.9
27.5°	201.8
30°	177.1
32.5°	155.8
35°	136.7
37.5°	119.9
40°	105.4
42.5°	93.0
45°	81.8
47.5°	72.9
50°	63.9
52.5°	56.0
55°	49.3
57.5°	43.7
60°	38.1
62.5°	32.5
65°	28.0
67.5°	23.5
70°	20.2
72.5°	15.7
75°	12.3
77.5°	9.0
80°	6.7
82.5°	3.4
85°	2.2
87.5°	0.0
90°	0.0

(END OF REPORT)