

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1344757

Luminaire Tested: P3A13R25W2N902750DE010 E3A451WMH_4000K

Issue Date: 2/13/2026

Test Information

Test Method: LM-79-2019
Report Number: P1344757
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-75)
Test Lab: INNOVATION CENTER
Issue Date: 2/13/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R25W2N902750DE010 E3A451WMH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 4000K CCT AND, 90CRI ,
E3A451WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 432.0 lumens
Efficiency: N/A
Efficacy: 35.1 lumens/watt
Spacing Criteria (0/90/45): 3.65 / 0.61 / 1.37
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1344757

CATALOG NUMBER: P3A13R25W2N902750DE010 E3A451WMH_4000K

Luminous Intensity Polar Plot



TEST NUMBER: P1344757

CATALOG NUMBER: P3A13R25W2N902750DE010 E3A451WMH_4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20				20
RC	80				70					50					30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	110	106	102	99	108	104	101	97	100	97	94	96	94	92	92	91	89	87	87
2	101	93	87	82	98	91	86	81	88	83	79	85	81	77	82	78	75	73	73
3	92	81	74	67	89	80	73	67	77	71	66	74	69	64	72	67	63	61	61
4	83	71	62	56	81	70	62	55	67	60	55	65	59	54	63	58	53	51	51
5	75	62	53	46	73	61	53	46	59	51	46	57	50	45	55	49	45	42	42
6	68	55	45	39	66	54	45	39	52	44	38	50	43	38	48	42	37	35	35
7	62	48	39	32	60	47	39	32	46	38	32	44	37	32	43	36	32	29	29
8	57	43	34	27	55	42	33	27	40	33	27	39	32	27	38	32	27	25	25
9	52	38	29	23	51	37	29	23	36	28	23	35	28	23	34	27	23	21	21
10	48	34	25	20	47	33	25	20	32	25	20	31	24	19	30	24	19	17	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°	135°	180°
0°	4824	4824	4824	4824	4824
5°	5525	5261	4689	4182	4094
10°	5500	4988	3986	3474	3474
15°	6129	4313	3110	2929	

TEST NUMBER: P1344757

CATALOG NUMBER: P3A13R25W2N902750DE010 E3A451WMH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	2.0	0.5
10°-20°	5.1	1.2
20°-30°	23.9	5.5
30°-40°	115.1	26.6
40°-50°	180.4	41.8
50°-60°	92.5	21.4
60°-70°	8.7	2.0
70°-80°	2.9	0.7
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	31.0	7.2
0°-40°	146.0	33.8
0°-60°	418.9	97.0
0°-90°	432.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	432.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	22	22	22	22	22	
5°	25	24	21	19	19	2
15°	27	19	14	13	14	11
25°	257	22	8	10	11	160
35°	1626	37	5	8	10	987
45°	2064	20	3	8	10	1510
55°	1054	3	3	7	10	877
65°	20	0	2	6	9	64
75°	1	0	2	5	7	1
85°	0	0	2	2	3	0
90°	0	0	0	0	0	

TEST NUMBER: P1344757

CATALOG NUMBER: P3A13R25W2N902750DE010 E3A451WMH_4000K

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	45°
0°	22.0	22.0	22.0	22.0	22.0	22.0	22.0	22.0	22.0	22.0	22.0
2.5°	23.9	23.9	23.9	23.9	23.9	23.9	23.6	23.6	23.9	23.6	23.6
5°	25.1	25.1	25.1	25.1	25.1	25.1	25.1	24.7	24.7	24.7	23.9
7.5°	25.5	25.1	25.1	25.1	25.1	25.1	25.1	25.1	24.7	24.7	23.6
10°	24.7	24.7	24.7	24.7	24.3	24.3	24.3	23.9	23.9	23.9	22.4
12.5°	24.7	24.7	24.7	24.7	24.3	24.3	23.9	23.9	23.6	23.2	20.5
15°	27.0	27.0	27.0	26.6	26.2	25.9	25.5	25.1	24.7	23.9	19.0
17.5°	39.5	38.4	38.0	36.5	34.6	32.7	31.2	29.7	28.1	27.0	18.2
20°	92.8	92.4	90.5	85.9	81.0	75.3	69.6	63.1	54.0	47.9	18.2
22.5°	160.8	158.5	155.1	151.7	142.9	132.7	122.0	109.9	98.1	85.5	19.4
25°	257.4	262.7	251.3	242.2	226.9	208.3	188.2	171.4	150.2	130.4	22.4
27.5°	447.4	450.9	428.4	398.8	363.4	324.3	286.3	257.7	222.0	189.3	28.1
30°	784.6	788.1	750.4	687.3	614.3	550.1	463.0	386.6	316.3	261.9	33.1
31°	979.3	952.7	908.9	847.7	755.4	658.4	553.9	461.5	372.5	301.1	34.6
32°	1148.4	1146.2	1095.2	1002.5	909.7	790.0	660.3	539.8	430.7	340.6	35.7
33°	1348.0	1332.8	1261.0	1173.5	1050.7	930.2	763.0	625.3	490.4	384.7	36.5
34°	1508.1	1467.0	1437.3	1337.4	1207.7	1054.2	875.1	715.8	564.9	427.3	36.9
35°	1625.5	1616.8	1559.0	1465.9	1333.9	1176.9	996.0	809.7	627		



TEST NUMBER: P1344757

CATALOG NUMBER: P3A13R25W2N902750DE010 E3A451WMH_4000K

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	45°
67.5°	2.7	2.3	2.3	2.3	1.9	1.9	1.9	1.9	1.5	1.5	0.4
70°	1.1	1.1	1.1	1.1	1.1	1.1	0.8	0.8	0.8	0.8	0.4
72.5°	1.1	1.1	1.1	0.8	0.8	0.8	0.8	0.8	0.8	0.4	0.4
75°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.4	0.4	0.4	0.4
77.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.4	0.4	0.4	0.4	0.4
80°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
82.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.8
85°	0.4	0.4	0.4	0.0	0.0	0.4	0.4	0.4	0.4	0.4	0.4
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.4
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P1344757

CATALOG NUMBER: P3A13R25W2N902750DE010 E3A451WMH_4000K

CANDELA DISTRIBUTION (continued):

	67.5°	90°	112.5°	135°	157.5°	180°
0°	22.0	22.0	22.0	22.0	22.0	22.0
2.5°	23.2	22.4	21.3	20.9	20.5	20.5
5°	22.8	21.3	20.1	19.0	18.6	18.6
7.5°	21.7	19.8	18.2	17.5	17.1	16.7
10°	20.5	17.9	16.3	15.6	15.6	15.6
12.5°	18.2	16.0	14.4	14.1	14.4	14.4
15°	16.3	13.7	12.9	12.9	13.3	13.7
17.5°	14.1	12.2	11.4	11.8	12.2	12.5
20°	12.5	10.3	10.3	10.6	11.8	11.8
22.5°	11.0	9.1	9.1	10.3	11.0	11.4
25°	9.9	8.0	8.4	9.5	10.6	11.0
27.5°	8.4	6.8	7.6	9.1	10.3	10.6
30°	7.2	6.1	7.2	8.7	9.9	10.6
31°	6.8	5.7	7.2	8.4	9.9	10.6
32°	6.1	5.7	6.8	8.4	9.9	10.3
33°	5.7	5.3	6.8	8.4	9.9	10.3
34°	5.3	4.9	6.5	8.4	9.9	10.3
35°	4.6	4.9	6.5	8.0	9.5	10.3
36°	4.2	4.6	6.5	8.0	9.5	10.3
37°	3.8	4.6	6.1	8.0	9.5	10.3
38°	3.4	4.2	6.1	8.0	9.5	10.3
39°	3.0	4.2	5.7	8.0	9.5	10.3
40°	2.7	3.8	5.7	7.6	9.5	10.3
41°	2.7	3.8	5.7	7.6	9.5	10.3
42°	2.3	3.8	5.7	7.6	9.5	10.3
43°	1.9	3.4	5.7	7.6	9.5	10.3
44°	1.5	3.4	5.3	7.6	9.5	10.3
45°	1.5	3.4	5.3	7.6	9.5	10.3
46°	1.1	3.0	5.3	7.6	9.5	10.3
47°	0.8	3.0	5.3	7.2	9.5	10.3
48°	0.8	3.0	5.3	7.2	9.5	10.3
49°	0.					



TEST NUMBER: P1344757

CATALOG NUMBER: P3A13R25W2N902750DE010 E3A451WMH_4000K

CANDELA DISTRIBUTION (continued):

	67.5°	90°	112.5°	135°	157.5°	180°
67.5°	0.8	1.9	3.8	5.7	8.4	8.7
70°	1.1	1.9	3.4	5.7	8.0	8.4
72.5°	1.1	1.9	3.4	4.9	7.2	8.0
75°	1.1	1.9	3.0	4.6	6.8	7.2
77.5°	1.1	1.9	2.7	4.2	6.1	6.5
80°	1.5	1.9	2.3	3.4	5.3	5.7
82.5°	1.5	1.9	1.9	2.7	4.2	4.6
85°	1.1	1.5	1.5	1.9	2.7	3.0
87.5°	1.1	1.5	1.1	0.8	1.5	1.5
90°	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)