

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296170

Luminaire Tested: P3A13R25W2N902765DE010 E3D1WMH_6500K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296170
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-9)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R25W2N902765DE010 E3D1WMH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R25 optic, 6500K CCT AND, 90CRI ,
E3D1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1043.0 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.4
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296170

CATALOG NUMBER: P3A13R25W2N902765DE010 E3D1WMH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1296170

CATALOG NUMBER: P3A13R25W2N902765DE010 E3D1WMH_6500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	110	113	111	110	108	107	106	105	104	103	102	100	99	99	97		
2	112	108	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	94		
3	109	104	101	98	107	103	100	97	100	98	96	98	96	94	96	94	93	92		
4	106	101	97	94	104	100	96	94	98	95	92	96	93	91	94	92	90	89		
5	103	97	93	91	101	96	93	90	95	92	90	93	91	89	92	90	88	87		
6	100	94	90	88	99	94	90	87	92	89	87	91	88	86	90	88	86	85		
7	98	92	88	85	97	91	87	85	90	87	84	89	86	84	88	86	84	83		
8	95	89	85	83	94	89	85	83	88	85	82	87	84	82	86	84	82	81		
9	93	87	83	81	92	86	83	80	86	83	80	85	82	80	84	82	80	79		
10	91	85	81	79	90	84	81	79	84	81	78	83	80	78	83	80	78	77		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1142277
5°	1058153
10°	818711
15°	391035
20°	128928
25°	54342
30°	21067
35°	9102
40°	3034
45°	1395
50°	512
55°	306
60°	175
65°	208
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1395 cd/sqm

TEST NUMBER: P1296170

CATALOG NUMBER: P3A13R25W2N902765DE010 E3D1WMH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	422.6	40.5
10°-20°	480.6	46.1
20°-30°	111.7	10.7
30°-40°	23.4	2.2
40°-50°	3.8	0.4
50°-60°	0.7	0.1
60°-70°	0.3	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1014.8	97.3
0°-40°	1038.2	99.5
0°-60°	1042.7	100.0
0°-90°	1043.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1043.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5209	
5°	4807	423
15°	1722	481
25°	225	112
35°	34	23
45°	4	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P1296170

CATALOG NUMBER: P3A13R25W2N902765DE010 E3D1WMH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	5209.2
1°	5198.6
2°	5144.5
3°	5068.5
4°	4952.4
5°	4807.2
6°	4620.8
7°	4425.7
8°	4206.7
9°	3959.8
10°	3676.9
11°	3349.0
12°	2972.7
13°	2560.6
14°	2129.4
15°	1722.5
16°	1362.5
17°	1061.5
18°	835.0
19°	667.8
20°	552.5
21°	461.7
22°	387.6
23°	323.7
24°	270.8
25°	224.6
27.5°	133.1
30°	83.2
32.5°	53.3
35°	34.0
37.5°	20.4
40°	10.6
42.5°	6.8
45°	4.5
47.5°	2.6
50°	1.5
52.5°	0.8
55°	0.8
57.5°	0.4
60°	0.4
62.5°	0.4
65°	0.4
67.5°	0.4
70°	0.0
72.5°	0.0



TEST NUMBER: P1296170

CATALOG NUMBER: P3A13R25W2N902765DE010 E3D1WMH_6500K

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)