

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1426531

Luminaire Tested: P3A13RH9030D2WDE010 E3HY1H

Issue Date: 3/9/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1426531  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-658-5)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13RH9030D2WDE010 E3HY1H  
Description: 3in Adjustable Dim to Warm LED luminaire with, RH optic, 3000K CCT AND, 90CRI , E3HY1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 704.0 lumens  
Efficiency: N/A  
Efficacy: 35.0 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.58  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 20.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1426531

CATALOG NUMBER: P3A13RH9030D2WDE010 E3HY1H

### Luminous Intensity Polar Plot



TEST NUMBER: P1426531

CATALOG NUMBER: P3A13RH9030D2WDE010 E3HY1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 114 | 112 | 109 | 107 | 112 | 110 | 108 | 106 | 106 | 104 | 103 |  | 102 | 101 | 99  |  | 98  |
| 2   | 109 | 105 | 102 | 99  | 107 | 103 | 100 | 97  | 100 | 98  | 95  |  | 97  | 95  | 93  |  | 95  |
| 3   | 105 | 99  | 95  | 91  | 103 | 98  | 94  | 91  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  |
| 4   | 100 | 94  | 89  | 85  | 99  | 93  | 88  | 85  | 91  | 87  | 84  |  | 89  | 85  | 83  |  | 87  |
| 5   | 96  | 89  | 84  | 80  | 95  | 88  | 83  | 80  | 86  | 82  | 79  |  | 85  | 81  | 78  |  | 83  |
| 6   | 92  | 84  | 79  | 76  | 91  | 84  | 79  | 75  | 82  | 78  | 75  |  | 81  | 77  | 74  |  | 80  |
| 7   | 88  | 80  | 75  | 72  | 87  | 80  | 75  | 71  | 79  | 74  | 71  |  | 77  | 74  | 71  |  | 76  |
| 8   | 85  | 77  | 71  | 68  | 84  | 76  | 71  | 68  | 75  | 71  | 68  |  | 74  | 70  | 67  |  | 73  |
| 9   | 82  | 73  | 68  | 65  | 81  | 73  | 68  | 65  | 72  | 67  | 64  |  | 71  | 67  | 64  |  | 70  |
| 10  | 79  | 70  | 65  | 62  | 78  | 70  | 65  | 62  | 69  | 65  | 61  |  | 68  | 64  | 61  |  | 68  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 311686 |
| 5°  | 293220 |
| 10° | 269779 |
| 15° | 244519 |
| 20° | 142369 |
| 25° | 93199  |
| 30° | 75201  |
| 35° | 37156  |
| 40° | 18778  |
| 45° | 8342   |
| 50° | 2217   |
| 55° | 421    |
| 60° | 0      |
| 65° | 0      |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 8342 cd/sqm

TEST NUMBER: P1426531

CATALOG NUMBER: P3A13RH9030D2WDE010 E3HY1H

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 123.2  | 17.5      |
| 10°-20°   | 275.6  | 39.1      |
| 20°-30°   | 183.7  | 26.1      |
| 30°-40°   | 97.0   | 13.8      |
| 40°-50°   | 22.8   | 3.2       |
| 50°-60°   | 1.6    | 0.2       |
| 60°-70°   | 0.0    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 582.5  | 82.7      |
| 0°-40°    | 679.6  | 96.5      |
| 0°-60°    | 704.0  | 100.0     |
| 0°-90°    | 704.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 704.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1421 |      |
| 5°  | 1332 | 123  |
| 15° | 1077 | 276  |
| 25° | 385  | 184  |
| 35° | 139  | 97   |
| 45° | 27   | 23   |
| 55° | 1    | 2    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P1426531

CATALOG NUMBER: P3A13RH9030D2WDE010 E3HY1H

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1421.4 |
| 2.5°  | 1398.8 |
| 5°    | 1332.1 |
| 7.5°  | 1262.2 |
| 10°   | 1211.6 |
| 12.5° | 1156.7 |
| 15°   | 1077.1 |
| 17.5° | 865.1  |
| 20°   | 610.1  |
| 22.5° | 437.9  |
| 25°   | 385.2  |
| 27.5° | 342.2  |
| 30°   | 297.0  |
| 32.5° | 221.7  |
| 35°   | 138.8  |
| 37.5° | 94.7   |
| 40°   | 65.6   |
| 42.5° | 43.0   |
| 45°   | 26.9   |
| 47.5° | 15.1   |
| 50°   | 6.5    |
| 52.5° | 3.2    |
| 55°   | 1.1    |
| 57.5° | 0.0    |
| 60°   | 0.0    |
| 62.5° | 0.0    |
| 65°   | 0.0    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)