

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296511

Luminaire Tested: P3A13R30W2N902765DE010 E3D1WH\_2700K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1296511  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-10)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R30W2N902765DE010 E3D1WH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI ,  
E3D1WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 875.0 lumens  
Efficiency: N/A  
Efficacy: 71.1 lumens/watt  
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.47  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296511

CATALOG NUMBER: P3A13R30W2N902765DE010 E3D1WH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1296511

CATALOG NUMBER: P3A13R30W2N902765DE010 E3D1WH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 115 | 113 | 111 | 109 | 113 | 111 | 109 | 108 | 107 | 106 | 104 |  | 103 | 102 | 101 |  | 100 |
| 2   | 111 | 108 | 105 | 102 | 109 | 106 | 103 | 101 | 103 | 101 | 99  |  | 100 | 98  | 97  |  | 97  |
| 3   | 108 | 103 | 100 | 97  | 106 | 102 | 99  | 96  | 99  | 97  | 95  |  | 97  | 95  | 93  |  | 95  |
| 4   | 105 | 99  | 95  | 92  | 103 | 98  | 95  | 92  | 96  | 93  | 91  |  | 94  | 92  | 90  |  | 93  |
| 5   | 101 | 96  | 92  | 89  | 100 | 95  | 91  | 88  | 93  | 90  | 87  |  | 92  | 89  | 87  |  | 90  |
| 6   | 99  | 92  | 88  | 85  | 97  | 92  | 88  | 85  | 90  | 87  | 85  |  | 89  | 86  | 84  |  | 88  |
| 7   | 96  | 89  | 85  | 82  | 95  | 89  | 85  | 82  | 88  | 84  | 82  |  | 87  | 84  | 81  |  | 86  |
| 8   | 93  | 87  | 83  | 80  | 92  | 86  | 82  | 80  | 85  | 82  | 79  |  | 84  | 81  | 79  |  | 84  |
| 9   | 91  | 84  | 80  | 77  | 90  | 84  | 80  | 77  | 83  | 79  | 77  |  | 82  | 79  | 77  |  | 82  |
| 10  | 88  | 82  | 78  | 75  | 88  | 81  | 78  | 75  | 81  | 77  | 75  |  | 80  | 77  | 75  |  | 80  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 696172 |
| 5°  | 687099 |
| 10° | 599900 |
| 15° | 381296 |
| 20° | 151073 |
| 25° | 50471  |
| 30° | 23472  |
| 35° | 10627  |
| 40° | 4093   |
| 45° | 2016   |
| 50° | 580    |
| 55° | 268    |
| 60° | 132    |
| 65° | 156    |
| 70° | 0      |
| 75° | 0      |
| 80° | 0      |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2016 cd/sqm

TEST NUMBER: P1296511

CATALOG NUMBER: P3A13R30W2N902765DE010 E3D1WH\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 285.4  | 32.6      |
| 10°-20°   | 442.6  | 50.6      |
| 20°-30°   | 114.1  | 13.0      |
| 30°-40°   | 26.8   | 3.1       |
| 40°-50°   | 5.2    | 0.6       |
| 50°-60°   | 0.6    | 0.1       |
| 60°-70°   | 0.3    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 842.1  | 96.2      |
| 0°-40°    | 868.9  | 99.3      |
| 0°-60°    | 874.7  | 100.0     |
| 0°-90°    | 875.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 875.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3175 |      |
| 5°  | 3122 | 285  |
| 15° | 1680 | 443  |
| 25° | 209  | 114  |
| 35° | 40   | 27   |
| 45° | 6    | 5    |
| 55° | 1    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1296511

CATALOG NUMBER: P3A13R30W2N902765DE010 E3D1WH\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 3174.8 |
| 1°    | 3172.4 |
| 2°    | 3165.0 |
| 3°    | 3156.5 |
| 4°    | 3143.9 |
| 5°    | 3121.5 |
| 6°    | 3085.1 |
| 7°    | 3024.7 |
| 8°    | 2942.2 |
| 9°    | 2834.5 |
| 10°   | 2694.2 |
| 11°   | 2527.4 |
| 12°   | 2345.4 |
| 13°   | 2135.8 |
| 14°   | 1916.4 |
| 15°   | 1679.6 |
| 16°   | 1447.6 |
| 17°   | 1224.1 |
| 18°   | 1009.8 |
| 19°   | 813.2  |
| 20°   | 647.4  |
| 21°   | 509.5  |
| 22°   | 400.8  |
| 23°   | 317.2  |
| 24°   | 254.1  |
| 25°   | 208.6  |
| 26°   | 173.9  |
| 27°   | 147.8  |
| 28°   | 127.7  |
| 29°   | 109.4  |
| 30°   | 92.7   |
| 32.5° | 58.4   |
| 35°   | 39.7   |
| 37.5° | 24.8   |
| 40°   | 14.3   |
| 42.5° | 9.5    |
| 45°   | 6.5    |
| 47.5° | 3.7    |
| 50°   | 1.7    |
| 52.5° | 0.7    |
| 55°   | 0.7    |
| 57.5° | 0.3    |
| 60°   | 0.3    |
| 62.5° | 0.3    |
| 65°   | 0.3    |



TEST NUMBER: P1296511

CATALOG NUMBER: P3A13R30W2N902765DE010 E3D1WH\_2700K

**CANDELA DISTRIBUTION (continued):**

|       | 0°  |
|-------|-----|
| 67.5° | 0.3 |
| 70°   | 0.0 |
| 72.5° | 0.0 |
| 75°   | 0.0 |
| 77.5° | 0.0 |
| 80°   | 0.0 |
| 82.5° | 0.0 |
| 85°   | 0.0 |
| 87.5° | 0.0 |
| 90°   | 0.0 |

(END OF REPORT)