

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296637

Luminaire Tested: P3A13R30W2N902765DE010 E3PHLD1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296637
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R30W2N902765DE010 E3PHLD1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 2700K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 539.0 lumens
Efficiency: N/A
Efficacy: 43.8 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296637
CATALOG NUMBER: P3A13R30W2N902765DE010 E3PHLD1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1296637

CATALOG NUMBER: P3A13R30W2N902765DE010 E3PHLD1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97	98	96	94	94	93	91	90
2	104	98	93	88	102	96	91	87	93	89	85	90	86	83	87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76	82	78	74	80	76	73	71
4	91	82	75	69	89	80	74	69	78	72	68	76	71	67	74	70	66	65
5	85	75	68	63	84	74	67	62	72	66	62	70	65	61	69	64	61	59
6	80	69	62	57	79	69	62	57	67	61	56	65	60	56	64	59	56	54
7	76	65	57	52	74	64	57	52	62	56	52	61	56	52	60	55	51	50
8	71	60	53	48	70	60	53	48	58	52	48	57	52	48	56	51	48	46
9	68	57	50	45	66	56	49	45	55	49	45	54	49	45	53	48	44	43
10	64	53	47	42	63	53	46	42	52	46	42	51	46	42	50	45	42	40

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	132818
5°	126942
10°	109506
15°	90761
20°	74393
25°	59979
30°	48337
35°	39592
40°	32890
45°	27910
50°	23880
55°	20644
60°	18420
65°	16085
70°	14105
75°	11861
80°	8840
85°	5032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 27910 cd/sqm



TEST NUMBER: P1296637

CATALOG NUMBER: P3A13R30W2N902765DE010 E3PHLD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	9.7
10°-20°	111.5	20.7
20°-30°	114.3	21.2
30°-40°	93.4	17.3
40°-50°	69.9	13.0
50°-60°	49.1	9.1
60°-70°	30.9	5.7
70°-80°	14.9	2.8
80°-90°	2.9	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	278.0	51.6
0°-40°	371.4	68.9
0°-60°	490.4	91.0
0°-90°	539.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	539.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	606	
5°	577	52
15°	400	111
25°	248	114
35°	148	93
45°	90	70
55°	54	49
65°	31	31
75°	14	15
85°	2	3
90°	0	



TEST NUMBER: P1296637
CATALOG NUMBER: P3A13R30W2N902765DE010 E3PHLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	605.7
2.5°	599.7
5°	576.7
7.5°	538.7
10°	491.8
12.5°	445.8
15°	399.8
17.5°	357.8
20°	318.8
22.5°	281.9
25°	247.9
27.5°	217.9
30°	190.9
32.5°	168.9
35°	147.9
37.5°	130.9
40°	114.9
42.5°	101.9
45°	90.0
47.5°	79.0
50°	70.0
52.5°	62.0
55°	54.0
57.5°	48.0
60°	42.0
62.5°	36.0
65°	31.0
67.5°	26.0
70°	22.0
72.5°	18.0
75°	14.0
77.5°	10.0
80°	7.0
82.5°	4.0
85°	2.0
87.5°	1.0
90°	0.0

(END OF REPORT)