

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296663

Luminaire Tested: P3A13R35W2N902750DE010 E3CB1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R35W2N902750DE010 E3CB1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 90CRI ,
E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 980.0 lumens
Efficiency: N/A
Efficacy: 79.7 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296663

CATALOG NUMBER: P3A13R35W2N902750DE010 E3CB1MW_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1296663

CATALOG NUMBER: P3A13R35W2N902750DE010 E3CB1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96		
2	111	107	104	101	109	105	103	100	102	100	98	99	98	96	97	95	94	93		
3	107	102	98	95	105	101	97	95	98	96	93	96	94	92	94	92	90	89		
4	104	98	94	91	102	97	93	90	95	92	89	93	90	88	91	89	87	86		
5	100	94	90	87	99	93	89	86	92	88	86	90	87	85	89	86	84	83		
6	97	91	86	83	96	90	86	83	89	85	82	87	84	82	86	83	81	80		
7	94	87	83	80	93	87	83	80	86	82	79	85	81	79	84	81	79	78		
8	91	84	80	77	90	84	80	77	83	79	77	82	79	76	81	78	76	75		
9	89	82	77	74	88	81	77	74	80	77	74	80	76	74	79	76	74	73		
10	86	79	75	72	85	79	75	72	78	74	72	77	74	72	77	74	71	70		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	639028
5°	626016
10°	582376
15°	426972
20°	218629
25°	78803
30°	30688
35°	10734
40°	4408
45°	1209
50°	1058
55°	1185
60°	1009
65°	778
70°	962
75°	1271
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 82.5°

Luminance: 1344 cd/sqm

TEST NUMBER: P1296663

CATALOG NUMBER: P3A13R35W2N902750DE010 E3CB1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	265.1	27.1
10°-20°	497.5	50.8
20°-30°	176.1	18.0
30°-40°	30.8	3.1
40°-50°	4.5	0.5
50°-60°	2.5	0.3
60°-70°	1.8	0.2
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	938.7	95.8
0°-40°	969.5	98.9
0°-60°	976.6	99.7
0°-90°	980.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	980.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2914	
5°	2844	265
15°	1881	497
25°	326	176
35°	40	31
45°	4	5
55°	3	3
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1296663

CATALOG NUMBER: P3A13R35W2N902750DE010 E3CB1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	2914.2
1°	2913.4
2°	2904.2
3°	2886.4
4°	2870.2
5°	2844.0
6°	2816.9
7°	2786.8
8°	2749.8
9°	2691.9
10°	2615.5
11°	2509.8
12°	2382.4
13°	2231.2
14°	2064.5
15°	1880.8
17.5°	1400.8
20°	936.9
22.5°	564.9
25°	325.7
27.5°	194.5
30°	121.2
32.5°	70.2
35°	40.1
37.5°	25.5
40°	15.4
42.5°	7.7
45°	3.9
47.5°	3.1
50°	3.1
52.5°	3.1
55°	3.1
57.5°	2.3
60°	2.3
62.5°	2.3
65°	1.5
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0



TEST NUMBER: P1296663

CATALOG NUMBER: P3A13R35W2N902750DE010 E3CB1MW_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)