

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296674

Luminaire Tested: P3A13R35W2N902750DE010 E3CD1MW\_2700K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1296674  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-20)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R35W2N902750DE010 E3CD1MW\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI ,  
E3CD1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 880.1 lumens  
Efficiency: N/A  
Efficacy: 71.6 lumens/watt  
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.52  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1296674

CATALOG NUMBER: P3A13R35W2N902750DE010 E3CD1MW\_2700K

### Luminous Intensity Polar Plot



TEST NUMBER: P1296674

CATALOG NUMBER: P3A13R35W2N902750DE010 E3CD1MW\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     |     | 0   |     |     |     | 0   |     |     |     | 0   |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 115 | 113 | 111 | 109 | 112 | 110 | 109 | 107 | 106 | 105 | 104 | 103 | 102 | 101 | 99  | 99  | 98  | 98  | 98  | 98  | 98  | 98  | 98  | 98  | 98  | 98  | 98  | 98  | 96  |
| 2   | 111 | 107 | 104 | 101 | 109 | 105 | 103 | 100 | 102 | 100 | 98  | 99  | 98  | 96  | 97  | 95  | 94  | 94  | 94  | 94  | 94  | 94  | 94  | 94  | 94  | 94  | 94  | 94  | 93  |
| 3   | 107 | 102 | 98  | 95  | 105 | 101 | 97  | 95  | 98  | 96  | 93  | 96  | 94  | 92  | 94  | 92  | 90  | 94  | 92  | 90  | 94  | 92  | 90  | 94  | 92  | 90  | 94  | 92  | 89  |
| 4   | 104 | 98  | 94  | 91  | 102 | 97  | 93  | 90  | 95  | 92  | 89  | 93  | 90  | 88  | 91  | 89  | 87  | 91  | 89  | 87  | 91  | 89  | 87  | 91  | 89  | 87  | 91  | 89  | 86  |
| 5   | 100 | 94  | 90  | 87  | 99  | 93  | 89  | 86  | 92  | 88  | 86  | 90  | 87  | 85  | 89  | 86  | 84  | 89  | 86  | 84  | 89  | 86  | 84  | 89  | 86  | 84  | 89  | 86  | 83  |
| 6   | 97  | 91  | 86  | 83  | 96  | 90  | 86  | 83  | 89  | 85  | 82  | 87  | 84  | 82  | 86  | 83  | 81  | 86  | 83  | 81  | 86  | 83  | 81  | 86  | 83  | 81  | 86  | 83  | 80  |
| 7   | 94  | 87  | 83  | 80  | 93  | 87  | 83  | 80  | 86  | 82  | 79  | 85  | 81  | 79  | 84  | 81  | 79  | 84  | 81  | 79  | 84  | 81  | 79  | 84  | 81  | 79  | 84  | 81  | 77  |
| 8   | 91  | 84  | 80  | 77  | 90  | 84  | 80  | 77  | 83  | 79  | 77  | 82  | 79  | 76  | 81  | 78  | 76  | 81  | 78  | 76  | 81  | 78  | 76  | 81  | 78  | 76  | 81  | 78  | 75  |
| 9   | 89  | 82  | 77  | 74  | 88  | 81  | 77  | 74  | 80  | 77  | 74  | 80  | 76  | 74  | 79  | 76  | 74  | 79  | 76  | 74  | 79  | 76  | 74  | 79  | 76  | 74  | 79  | 76  | 73  |
| 10  | 86  | 79  | 75  | 72  | 85  | 79  | 75  | 72  | 78  | 74  | 72  | 77  | 74  | 72  | 77  | 74  | 71  | 77  | 74  | 71  | 77  | 74  | 71  | 77  | 74  | 71  | 77  | 74  | 70  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 573814 |
| 5°  | 562138 |
| 10° | 522947 |
| 15° | 383407 |
| 20° | 196320 |
| 25° | 70770  |
| 30° | 27549  |
| 35° | 9637   |
| 40° | 3979   |
| 45° | 1085   |
| 50° | 955    |
| 55° | 1070   |
| 60° | 921    |
| 65° | 726    |
| 70° | 898    |
| 75° | 1186   |
| 80° | 884    |
| 85° | 0      |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 75°  
Luminance: 1186 cd/sqm

TEST NUMBER: P1296674

CATALOG NUMBER: P3A13R35W2N902750DE010 E3CD1MW\_2700K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 238.1  | 27.1      |
| 10°-20°   | 446.7  | 50.8      |
| 20°-30°   | 158.1  | 18.0      |
| 30°-40°   | 27.7   | 3.1       |
| 40°-50°   | 4.1    | 0.5       |
| 50°-60°   | 2.3    | 0.3       |
| 60°-70°   | 1.6    | 0.2       |
| 70°-80°   | 1.2    | 0.1       |
| 80°-90°   | 0.3    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 842.9  | 95.8      |
| 0°-40°    | 870.6  | 98.9      |
| 0°-60°    | 876.9  | 99.6      |
| 0°-90°    | 880.1  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 880.1  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 2617 |      |
| 5°  | 2554 | 238  |
| 15° | 1689 | 447  |
| 25° | 292  | 158  |
| 35° | 36   | 28   |
| 45° | 4    | 4    |
| 55° | 3    | 2    |
| 65° | 1    | 2    |
| 75° | 1    | 1    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1296674

CATALOG NUMBER: P3A13R35W2N902750DE010 E3CD1MW\_2700K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 2616.8 |
| 1°    | 2616.1 |
| 2°    | 2607.8 |
| 3°    | 2591.9 |
| 4°    | 2577.3 |
| 5°    | 2553.8 |
| 6°    | 2529.5 |
| 7°    | 2502.5 |
| 8°    | 2469.2 |
| 9°    | 2417.2 |
| 10°   | 2348.6 |
| 11°   | 2253.7 |
| 12°   | 2139.3 |
| 13°   | 2003.5 |
| 14°   | 1853.8 |
| 15°   | 1688.9 |
| 17.5° | 1257.8 |
| 20°   | 841.3  |
| 22.5° | 507.3  |
| 25°   | 292.5  |
| 27.5° | 174.6  |
| 30°   | 108.8  |
| 32.5° | 63.1   |
| 35°   | 36.0   |
| 37.5° | 22.9   |
| 40°   | 13.9   |
| 42.5° | 6.9    |
| 45°   | 3.5    |
| 47.5° | 2.8    |
| 50°   | 2.8    |
| 52.5° | 2.8    |
| 55°   | 2.8    |
| 57.5° | 2.1    |
| 60°   | 2.1    |
| 62.5° | 2.1    |
| 65°   | 1.4    |
| 67.5° | 1.4    |
| 70°   | 1.4    |
| 72.5° | 1.4    |
| 75°   | 1.4    |
| 77.5° | 0.7    |
| 80°   | 0.7    |
| 82.5° | 0.7    |
| 85°   | 0.0    |
| 87.5° | 0.0    |



TEST NUMBER: P1296674

CATALOG NUMBER: P3A13R35W2N902750DE010 E3CD1MW\_2700K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)