

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1339861

Luminaire Tested: P3A09R159030D2WDE010 E3A301WH

Issue Date: 2/13/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1339861  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2510-583-59)  
Test Lab: INNOVATION CENTER  
Issue Date: 2/13/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A09R159030D2WDE010 E3A301WH  
Description: 3in Adjustable Dim to Warm LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,  
E3A301WH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 337.0 lumens  
Efficiency: N/A  
Efficacy: 22.9 lumens/watt  
Spacing Criteria (0/90/45): 2.35 / 0.49 / 1.26  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 14.7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1339861

CATALOG NUMBER: P3A09R159030D2WDE010 E3A301WH

### Luminous Intensity Polar Plot



TEST NUMBER: P1339861

CATALOG NUMBER: P3A09R159030D2WDE010 E3A301WH

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 102 | 102 | 100 |
| 1   | 113 | 109 | 107 | 104 | 110 | 107 | 105 | 102 | 103 | 101 | 99  | 99  | 98  | 96  | 96  | 95  | 93  | 93  | 93  | 92  |
| 2   | 106 | 100 | 96  | 92  | 104 | 99  | 94  | 91  | 95  | 92  | 89  | 92  | 89  | 87  | 89  | 87  | 85  | 85  | 85  | 83  |
| 3   | 99  | 92  | 86  | 81  | 97  | 90  | 85  | 81  | 88  | 83  | 79  | 85  | 81  | 78  | 83  | 80  | 77  | 77  | 77  | 75  |
| 4   | 93  | 84  | 78  | 73  | 91  | 83  | 77  | 72  | 81  | 75  | 71  | 79  | 74  | 70  | 77  | 73  | 70  | 70  | 70  | 68  |
| 5   | 87  | 77  | 70  | 65  | 85  | 76  | 70  | 65  | 74  | 69  | 64  | 72  | 67  | 64  | 71  | 66  | 63  | 63  | 63  | 61  |
| 6   | 81  | 71  | 64  | 59  | 80  | 70  | 63  | 58  | 68  | 62  | 58  | 67  | 61  | 57  | 65  | 61  | 57  | 57  | 57  | 55  |
| 7   | 76  | 65  | 58  | 53  | 74  | 64  | 57  | 53  | 63  | 57  | 52  | 61  | 56  | 52  | 60  | 55  | 52  | 52  | 52  | 50  |
| 8   | 71  | 60  | 53  | 48  | 70  | 59  | 52  | 48  | 58  | 52  | 47  | 57  | 51  | 47  | 56  | 51  | 47  | 47  | 47  | 45  |
| 9   | 66  | 55  | 48  | 43  | 65  | 54  | 48  | 43  | 53  | 47  | 43  | 52  | 47  | 43  | 51  | 46  | 42  | 42  | 42  | 41  |
| 10  | 62  | 51  | 44  | 39  | 61  | 50  | 43  | 39  | 49  | 43  | 39  | 48  | 43  | 39  | 47  | 42  | 39  | 39  | 39  | 37  |

**AVERAGE LUMINANCE (cd/sqm):**

|     | 0°     | 45°   | 90°  | 135° | 180° |
|-----|--------|-------|------|------|------|
| 0°  | 2434   | 2434  | 2434 | 2434 | 2434 |
| 5°  | 5261   | 3896  | 2311 | 1233 | 1013 |
| 10° | 23357  | 7370  | 1826 | 512  | 356  |
| 15° | 88332  | 17049 | 1271 | 227  | 159  |
| 20° | 339716 | 24012 | 770  | 70   | 70   |
| 25° | 646029 | 22525 | 387  | 0    | 0    |
| 30° | 780399 | 18180 | 177  | 0    | 0    |
| 35° | 608652 | 12367 | 80   | 0    | 0    |
| 40° | 222102 | 6097  | 86   | 0    | 86   |
| 45° | 57029  | 1830  | 93   | 0    | 217  |
| 50° | 9620   | 239   | 102  | 102  | 341  |
| 55° | 1262   | 0     | 268  | 382  | 612  |
| 60° | 132    | 132   | 439  | 570  | 877  |
| 65° | 156    | 156   | 675  | 830  | 1038 |
| 70° | 192    | 192   | 833  | 833  | 1026 |
| 75° | 254    | 254   | 1101 | 847  | 1101 |
| 80° | 0      | 379   | 1263 | 884  | 1263 |
| 85° | 0      | 755   | 2516 | 755  | 755  |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 57029 cd/sqm

TEST NUMBER: P1339861

CATALOG NUMBER: P3A09R159030D2WDE010 E3A301WH

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 1.5    | 0.5       |
| 10°-20°   | 25.8   | 7.7       |
| 20°-30°   | 143.2  | 42.5      |
| 30°-40°   | 138.4  | 41.1      |
| 40°-50°   | 24.1   | 7.1       |
| 50°-60°   | 1.7    | 0.5       |
| 60°-70°   | 1.0    | 0.3       |
| 70°-80°   | 0.8    | 0.2       |
| 80°-90°   | 0.4    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 170.6  | 50.6      |
| 0°-40°    | 308.9  | 91.7      |
| 0°-60°    | 334.7  | 99.3      |
| 0°-90°    | 337.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 337.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | 45° | 90° | 135° | 180° | Flux |
|-----|------|-----|-----|------|------|------|
| 0°  | 11   | 11  | 11  | 11   | 11   |      |
| 5°  | 24   | 18  | 10  | 6    | 5    | 5    |
| 15° | 389  | 75  | 6   | 1    | 1    | 173  |
| 25° | 2670 | 93  | 2   | 0    | 0    | 1194 |
| 35° | 2274 | 46  | 0   | 0    | 0    | 1308 |
| 45° | 184  | 6   | 0   | 0    | 1    | 198  |
| 55° | 3    | 0   | 1   | 1    | 2    | 6    |
| 65° | 0    | 0   | 1   | 2    | 2    | 0    |
| 75° | 0    | 0   | 1   | 1    | 1    | 0    |
| 85° | 0    | 0   | 1   | 0    | 0    | 0    |
| 90° | 0    | 0   | 0   | 0    | 0    |      |

TEST NUMBER: P1339861

CATALOG NUMBER: P3A09R159030D2WDE010 E3A301WH

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     | 2.5°   | 5°     | 7.5°   | 10°    | 12.5°  | 15°    | 17.5°  | 20°    | 22.5° | 45°   |
|-------|--------|--------|--------|--------|--------|--------|--------|--------|--------|-------|-------|
| 0°    | 11.1   | 11.1   | 11.1   | 11.1   | 11.1   | 11.1   | 11.1   | 11.1   | 11.1   | 11.1  | 11.1  |
| 2.5°  | 16.4   | 15.7   | 16.1   | 16.1   | 16.1   | 16.1   | 16.1   | 15.4   | 15.4   | 15.7  | 14.1  |
| 5°    | 23.9   | 23.9   | 23.6   | 23.9   | 23.9   | 23.6   | 22.9   | 22.6   | 22.6   | 22.0  | 17.7  |
| 7.5°  | 47.9   | 47.2   | 47.2   | 46.5   | 43.3   | 42.3   | 41.6   | 40.0   | 37.0   | 36.4  | 22.9  |
| 10°   | 104.9  | 105.2  | 102.9  | 100.0  | 99.7   | 94.7   | 93.1   | 90.1   | 84.6   | 79.0  | 33.1  |
| 12.5° | 190.5  | 186.2  | 180.6  | 181.0  | 171.4  | 168.2  | 160.6  | 152.4  | 143.9  | 135.1 | 54.4  |
| 15°   | 389.1  | 377.0  | 384.2  | 366.5  | 346.5  | 323.9  | 300.9  | 272.1  | 247.5  | 221.3 | 75.1  |
| 17.5° | 819.5  | 831.3  | 811.3  | 735.6  | 689.1  | 634.3  | 557.3  | 482.9  | 419.3  | 368.1 | 91.8  |
| 20°   | 1455.8 | 1473.2 | 1405.3 | 1339.5 | 1226.4 | 1103.1 | 974.6  | 829.0  | 689.7  | 569.1 | 102.9 |
| 21°   | 1721.7 | 1711.2 | 1683.3 | 1577.8 | 1447.3 | 1304.4 | 1147.0 | 986.4  | 817.6  | 660.9 | 103.9 |
| 22°   | 1978.7 | 1983.6 | 1918.7 | 1808.2 | 1672.5 | 1514.2 | 1322.1 | 1123.8 | 941.8  | 735.6 | 102.3 |
| 23°   | 2234.7 | 2250.5 | 2164.6 | 2061.0 | 1890.2 | 1711.5 | 1489.3 | 1275.2 | 1050.3 | 821.2 | 99.0  |
| 24°   | 2471.7 | 2460.9 | 2402.9 | 2272.4 | 2089.8 | 1880.7 | 1649.9 | 1390.3 | 1139.5 | 894.3 | 96.4  |
| 25°   | 2670.1 | 2668.8 | 2577.6 | 2450.8 | 2241.9 | 2010.2 | 1755.8 | 1484.4 | 1215.9 | 943.8 | 93.1  |
| 26°   | 2832.3 | 2805.8 | 2734.0 | 2579.3 | 2373.1 | 2128.5 | 1842.7 | 1552.9 | 1258.8 | 968.7 | 89.8  |
| 27°   | 2957.6 | 2938.5 | 2842.2 | 2681.2 | 2465.8 | 2195.4 | 1898.4 | 1587.0 | 1278.5 | 976.9 | 85.6  |
| 28°   | 3041.8 | 3021.2 | 2918.5 | 2752.7 | 2517.0 | 2237.3 | 1927.9 | 1601.4 | 1278.5 | 969.0 | 81.6  |
| 29°   | 3085.4 | 3057.2 | 2954.9 | 2777.3 | 2528.8 | 2242.3 | 1920.7 | 1587.3 | 1258.5 | 944.8 | 77.0  |
| 30°   | 3082.1 | 3047.1 | 2939.9 | 2755.0 | 2493.7 | 2201.9 | 1880.4 | 1536.5 | 1213.2 | 908.7 | 71.8  |
| 31°   | 3029.0 | 2989.7 | 2870.0 | 2679.6 | 2421.3 | 2125.9 | 1804.3 | 1468.3 | 1151.3 | 861.8 | 66.5  |
| 32°   | 2921.2 | 2871.3 | 2754.6 | 2564.8 | 2309.8 | 2012.1 | 1693.8 | 1363.1 | 1058.5 | 793.3 | 61.0  |
| 33°   | 2745.5 | 2695.3 | 2570.1 | 2392.1 | 2159.0 | 1867.9 | 1547.3 | 1250.0 | 953.0  | 711.7 | 56.4  |
| 34°   | 2525.5 | 2479.6 | 2371.8 | 2192.4 | 1968.9 | 1685.3 | 1378.8 | 1093.6 | 843.5  | 630.7 | 51.5  |
| 35°   | 2273.7 | 2200.6 | 2102.9 | 1961.0 | 1743.0 | 1457.8 | 1196.9 | 948.0  | 730.7  | 545.8 | 46.2  |
| 36°   | 1933.1 | 1946.2 | 1842.7 | 1668.9 | 1488.3 | 1264.7 | 1014.3 | 790.4  | 611.0  | 465.2 | 41.6  |
| 37°   | 1631.2 | 1610.6 | 1544.7 | 1410.3 | 1252.9 | 1031.0 | 850.0  | 670.1  | 514.0  | 393.4 | 36.7  |
| 38°   | 1315.9 | 1320.4 | 1255.9 | 1152.6 | 996.6  | 847.7  | 684.2  | 550.4  | 430.1  | 334.7 | 32.1  |
| 39°   | 1030.0 | 1026.4 | 1009.0 | 913.3  | 772.0  | 674.3  | 554.3  | 456.3  | 358.3  | 282.2 | 27.2  |
| 40°   | 775.9  | 781.8  | 741.2  | 683.5  | 601.2  | 520.9  | 441.6  | 363.9  | 296.3  | 238.0 | 21.3  |
| 42.5° | 377.3  | 386.5  | 359.6  | 344.9  | 308.5  | 277.0  | 233.7  | 190.8  | 162.3  | 140.3 | 9.5   |
| 45°   | 183.9  | 178.7  | 176.4  | 169.2  | 160.6  | 143.6  | 127.2  | 109.2  | 95.4   | 82.3  | 5.9   |
| 47.5° | 94.1   | 91.5   | 91.5   | 88.5   | 85.6   | 80.0   | 71.8   | 65.9   | 59.3   | 51.1  | 2.3   |
| 50°   | 28.2   | 27.9   | 27.5   | 27.9   | 26.9   | 27.9   | 28.5   | 28.8   | 26.2   | 25.9  | 0.7   |
| 52.5° | 11.1   | 11.5   | 11.1   | 12.1   | 12.1   | 11.8   | 12.1   | 11.8   | 11.5   | 10.2  | 0.0   |
| 55°   | 3.3    | 3.3    | 3.3    | 3.3    | 3.3    | 3.3    | 3.6    | 3.9    | 3.6    | 3.9   | 0.0   |
| 57.5° | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7    | 0.7   | 0.0   |
| 60°   | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.0   | 0.3   |
| 62.5° | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3   | 0.3   |
| 65°   | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3   | 0.3   |
| 67.5° | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3   | 0.3   |
| 70°   | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3   | 0.3   |
| 72.5° | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3   | 0.3   |
| 75°   | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3    | 0.3   | 0.3   |
| 77.5° | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.3    | 0.3   | 0.3   |
| 80°   | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0    | 0.0   | 0.3   |



TEST NUMBER: P1339861

CATALOG NUMBER: P3A09R159030D2WDE010 E3A301WH

**CANDELA DISTRIBUTION (continued):**

|       | 0°  | 2.5° | 5°  | 7.5° | 10° | 12.5° | 15° | 17.5° | 20° | 22.5° | 45° |
|-------|-----|------|-----|------|-----|-------|-----|-------|-----|-------|-----|
| 82.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.3 |
| 85°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.3 |
| 87.5° | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.3 |
| 90°   | 0.0 | 0.0  | 0.0 | 0.0  | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 | 0.0   | 0.0 |

TEST NUMBER: P1339861

CATALOG NUMBER: P3A09R159030D2WDE010 E3A301WH

**CANDELA DISTRIBUTION (continued):**

|       | 67.5° | 90°  | 112.5° | 135° | 157.5° | 180° |
|-------|-------|------|--------|------|--------|------|
| 0°    | 11.1  | 11.1 | 11.1   | 11.1 | 11.1   | 11.1 |
| 2.5°  | 13.1  | 11.5 | 9.5    | 7.9  | 7.2    | 6.9  |
| 5°    | 14.1  | 10.5 | 7.2    | 5.6  | 4.9    | 4.6  |
| 7.5°  | 15.1  | 9.5  | 5.6    | 3.9  | 3.0    | 2.6  |
| 10°   | 15.7  | 8.2  | 4.3    | 2.3  | 1.6    | 1.6  |
| 12.5° | 15.7  | 6.6  | 3.0    | 1.3  | 1.0    | 1.0  |
| 15°   | 15.4  | 5.6  | 2.0    | 1.0  | 0.7    | 0.7  |
| 17.5° | 15.1  | 4.3  | 1.3    | 0.7  | 0.3    | 0.7  |
| 20°   | 14.1  | 3.3  | 0.7    | 0.3  | 0.3    | 0.3  |
| 21°   | 13.8  | 3.0  | 0.7    | 0.3  | 0.3    | 0.3  |
| 22°   | 13.1  | 2.6  | 0.3    | 0.0  | 0.3    | 0.3  |
| 23°   | 12.5  | 2.0  | 0.3    | 0.0  | 0.0    | 0.0  |
| 24°   | 11.5  | 1.6  | 0.3    | 0.0  | 0.0    | 0.0  |
| 25°   | 10.8  | 1.6  | 0.3    | 0.0  | 0.0    | 0.0  |
| 26°   | 10.2  | 1.0  | 0.0    | 0.0  | 0.0    | 0.0  |
| 27°   | 9.2   | 0.7  | 0.0    | 0.0  | 0.0    | 0.0  |
| 28°   | 8.5   | 0.7  | 0.0    | 0.0  | 0.0    | 0.0  |
| 29°   | 7.5   | 0.7  | 0.0    | 0.0  | 0.0    | 0.0  |
| 30°   | 6.6   | 0.7  | 0.0    | 0.0  | 0.0    | 0.0  |
| 31°   | 5.2   | 0.3  | 0.0    | 0.0  | 0.0    | 0.0  |
| 32°   | 4.3   | 0.3  | 0.0    | 0.0  | 0.0    | 0.0  |
| 33°   | 3.0   | 0.3  | 0.0    | 0.0  | 0.0    | 0.0  |
| 34°   | 2.0   | 0.3  | 0.0    | 0.0  | 0.0    | 0.0  |
| 35°   | 1.6   | 0.3  | 0.0    | 0.0  | 0.0    | 0.0  |
| 36°   | 1.0   | 0.3  | 0.0    | 0.0  | 0.0    | 0.3  |
| 37°   | 1.0   | 0.3  | 0.0    | 0.0  | 0.0    | 0.3  |
| 38°   | 0.7   | 0.3  | 0.0    | 0.0  | 0.0    | 0.3  |
| 39°   | 0.3   | 0.3  | 0.0    | 0.0  | 0.0    | 0.3  |
| 40°   | 0.3   | 0.3  | 0.0    | 0.0  | 0.0    | 0.3  |
| 42.5° | 0.0   | 0.3  | 0.0    | 0.0  | 0.3    | 0.7  |
| 45°   | 0.0   | 0.3  | 0.0    | 0.0  | 0.3    | 0.7  |
| 47.5° | 0.0   | 0.3  | 0.0    | 0.0  | 0.7    | 0.7  |
| 50°   | 0.0   | 0.3  | 0.3    | 0.3  | 0.7    | 1.0  |
| 52.5° | 0.0   | 0.7  | 0.3    | 0.7  | 1.0    | 1.3  |
| 55°   | 0.3   | 0.7  | 0.7    | 1.0  | 1.3    | 1.6  |
| 57.5° | 0.3   | 1.0  | 1.0    | 1.3  | 1.6    | 1.6  |
| 60°   | 0.7   | 1.0  | 1.3    | 1.3  | 2.0    | 2.0  |
| 62.5° | 0.7   | 1.3  | 1.3    | 1.3  | 2.0    | 2.0  |
| 65°   | 0.7   | 1.3  | 1.3    | 1.6  | 2.0    | 2.0  |
| 67.5° | 0.7   | 1.3  | 1.3    | 1.3  | 1.6    | 2.0  |
| 70°   | 0.7   | 1.3  | 1.0    | 1.3  | 1.6    | 1.6  |
| 72.5° | 0.7   | 1.3  | 1.0    | 1.0  | 1.3    | 1.6  |
| 75°   | 0.7   | 1.3  | 1.0    | 1.0  | 1.3    | 1.3  |
| 77.5° | 0.7   | 1.0  | 1.0    | 0.7  | 1.0    | 1.0  |
| 80°   | 0.7   | 1.0  | 0.7    | 0.7  | 1.0    | 1.0  |



TEST NUMBER: P1339861

CATALOG NUMBER: P3A09R159030D2WDE010 E3A301WH

**CANDELA DISTRIBUTION (continued):**

|       | 67.5° | 90° | 112.5° | 135° | 157.5° | 180° |
|-------|-------|-----|--------|------|--------|------|
| 82.5° | 0.7   | 1.0 | 0.7    | 0.3  | 0.7    | 0.7  |
| 85°   | 0.7   | 1.0 | 0.7    | 0.3  | 0.3    | 0.3  |
| 87.5° | 0.7   | 1.0 | 0.3    | 0.0  | 0.0    | 0.3  |
| 90°   | 0.0   | 0.0 | 0.0    | 0.0  | 0.0    | 0.0  |

(END OF REPORT)