

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296849

Luminaire Tested: P3A13R35W2N902765DE010 E3DL1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296849
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-19)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R35W2N902765DE010 E3DL1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 2700K CCT AND, 90CRI ,
E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 728.1 lumens
Efficiency: N/A
Efficacy: 59.2 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.58
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296849
CATALOG NUMBER: P3A13R35W2N902765DE010 E3DL1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1296849

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DL1MW_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	96	96	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	91	91	91	90
3	105	99	95	91	103	98	94	90	95	92	89	93	90	88	91	88	86	86	86	86	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	82	82	82	80
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	78	78	78	76
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	74	74	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	71	71	71	70
8	85	77	72	69	84	77	72	68	76	71	68	75	71	68	74	70	68	68	68	68	66
9	82	74	69	66	81	74	69	65	73	68	65	72	68	65	71	67	65	65	65	65	64
10	79	71	66	63	78	71	66	63	70	66	63	69	65	62	69	65	62	62	62	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	367164
5°	352872
10°	307454
15°	235484
20°	157560
25°	95328
30°	54717
35°	30597
40°	16259
45°	8373
50°	4025
55°	3173
60°	3026
65°	2491
70°	2693
75°	2372
80°	2652
85°	1761

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8373 cd/sqm



TEST NUMBER: P1296849

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DL1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	145.9	20.0
10°-20°	282.7	38.8
20°-30°	185.1	25.4
30°-40°	75.1	10.3
40°-50°	22.5	3.1
50°-60°	7.6	1.1
60°-70°	5.1	0.7
70°-80°	3.0	0.4
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	613.6	84.3
0°-40°	688.7	94.6
0°-60°	718.8	98.7
0°-90°	728.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	728.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1674	
5°	1603	146
15°	1037	283
25°	394	185
35°	114	75
45°	27	23
55°	8	8
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1296849

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DL1MW_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1674.4
1°	1671.7
2°	1664.0
3°	1648.8
4°	1630.8
5°	1603.1
6°	1568.5
7°	1529.7
8°	1486.1
9°	1436.2
10°	1380.8
11°	1319.2
12°	1254.8
13°	1182.8
14°	1114.2
15°	1037.3
17.5°	851.1
20°	675.2
22.5°	519.4
25°	394.0
27.5°	293.6
30°	216.1
32.5°	158.6
35°	114.3
37.5°	81.0
40°	56.8
42.5°	39.5
45°	27.0
47.5°	18.0
50°	11.8
52.5°	9.0
55°	8.3
57.5°	7.6
60°	6.9
62.5°	6.2
65°	4.8
67.5°	4.2
70°	4.2
72.5°	3.5
75°	2.8
77.5°	2.1
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7



TEST NUMBER: P1296849
CATALOG NUMBER: P3A13R35W2N902765DE010 E3DL1MW_2700K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)