

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296871

Luminaire Tested: P3A13R35W2N902765DE010 E3DLD1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296871
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R35W2N902765DE010 E3DLD1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 5000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 306.0 lumens
Efficiency: N/A
Efficacy: 24.9 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296871
CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLD1GPH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1296871

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLD1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20						20							20
RC	80					70						30							10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50
RCR																			
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102
1	112	109	106	104		110	107	104	102		103	101	99		99	98	96		96
2	106	100	96	92		104	98	94	91		95	92	89		92	89	87		89
3	100	92	87	82		98	91	86	81		88	84	80		86	82	79		83
4	94	85	79	74		92	84	78	74		82	77	73		80	75	72		78
5	89	79	73	68		87	78	72	67		76	71	67		75	70	66		73
6	84	74	67	62		82	73	67	62		71	66	61		70	65	61		68
7	79	69	62	57		78	68	62	57		67	61	57		65	60	57		64
8	75	64	58	53		74	64	57	53		63	57	53		62	56	53		61
9	71	60	54	50		70	60	54	50		59	53	49		58	53	49		57
10	67	57	51	46		66	56	50	46		56	50	46		55	50	46		54

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	69907
5°	68413
10°	64083
15°	57526
20°	50031
25°	42631
30°	35702
35°	28456
40°	20553
45°	13025
50°	7096
55°	4932
60°	4649
65°	4307
70°	4103
75°	3558
80°	3283
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 13025 cd/sqm



TEST NUMBER: P1296871

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLD1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.9	9.5
10°-20°	70.5	23.0
20°-30°	80.8	26.4
30°-40°	65.9	21.5
40°-50°	33.3	10.9
50°-60°	12.3	4.0
60°-70°	8.3	2.7
70°-80°	4.6	1.5
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	180.2	58.9
0°-40°	246.2	80.4
0°-60°	291.8	95.3
0°-90°	306.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	306.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	319	
5°	311	29
15°	253	71
25°	176	81
35°	106	66
45°	42	33
55°	13	12
65°	8	8
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1296871
CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLD1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	318.8
1°	318.4
2°	317.6
3°	316.1
4°	313.9
5°	310.8
6°	307.0
7°	303.3
8°	298.3
9°	293.4
10°	287.8
11°	281.7
12°	275.3
13°	268.1
14°	260.5
15°	253.4
17.5°	234.1
20°	214.4
22.5°	194.4
25°	176.2
27.5°	158.4
30°	141.0
32.5°	123.6
35°	106.3
37.5°	88.9
40°	71.8
42.5°	56.0
45°	42.0
47.5°	30.3
50°	20.8
52.5°	15.1
55°	12.9
57.5°	11.7
60°	10.6
62.5°	9.5
65°	8.3
67.5°	7.2
70°	6.4
72.5°	5.3
75°	4.2
77.5°	3.4
80°	2.6
82.5°	1.9
85°	1.1
87.5°	0.8



TEST NUMBER: P1296871
CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLD1GPH_5000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)