

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1296898

Luminaire Tested: P3A13R35W2N902765DE010 E3DLD1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1296898
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-18)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R35W2N902765DE010 E3DLD1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R35 optic, 3000K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 618.0 lumens
Efficiency: N/A
Efficacy: 50.2 lumens/watt
Spacing Criteria (0/90/45): 0.8 / 0.8 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1296898

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLD1WMH_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1296898

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLD1WMH_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93		91
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89	87	85		83
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83	80	78		76
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78	74	71		69
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73	69	66		64
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68	64	61		59
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64	60	56		55
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61	56	52		51
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57	52	49		48
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54	49	46		45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	141173
5°	138168
10°	129412
15°	116164
20°	101042
25°	86110
30°	72138
35°	57447
40°	41535
45°	26297
50°	14328
55°	9940
60°	9385
65°	8717
70°	8335
75°	7117
80°	6693
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 26297 cd/sqm

TEST NUMBER: P1296898

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLD1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.4	9.5
10°-20°	142.4	23.0
20°-30°	163.2	26.4
30°-40°	133.2	21.5
40°-50°	67.1	10.9
50°-60°	24.9	4.0
60°-70°	16.7	2.7
70°-80°	9.3	1.5
80°-90°	2.8	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.0	58.9
0°-40°	497.1	80.4
0°-60°	589.2	95.3
0°-90°	618.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	618.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	644	
5°	628	58
15°	512	142
25°	356	163
35°	215	133
45°	85	67
55°	26	25
65°	17	17
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1296898

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLD1WMH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	643.8
1°	643.0
2°	641.5
3°	638.4
4°	633.9
5°	627.7
6°	620.1
7°	612.5
8°	602.5
9°	592.6
10°	581.2
11°	568.9
12°	556.0
13°	541.5
14°	526.2
15°	511.7
17.5°	472.7
20°	433.0
22.5°	392.5
25°	355.9
27.5°	320.0
30°	284.9
32.5°	249.7
35°	214.6
37.5°	179.5
40°	145.1
42.5°	113.0
45°	84.8
47.5°	61.1
50°	42.0
52.5°	30.5
55°	26.0
57.5°	23.7
60°	21.4
62.5°	19.1
65°	16.8
67.5°	14.5
70°	13.0
72.5°	10.7
75°	8.4
77.5°	6.9
80°	5.3
82.5°	3.8
85°	2.3
87.5°	1.5



TEST NUMBER: P1296898

CATALOG NUMBER: P3A13R35W2N902765DE010 E3DLD1WMH_3000K

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)