

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295331

Luminaire Tested: P3A13R15W2N902750DE010 E3CD1MMS_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295331
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-4)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R15W2N902750DE010 E3CD1MMS_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 5000K CCT AND, 90CRI ,
E3CD1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 976.0 lumens
Efficiency: N/A
Efficacy: 79.3 lumens/watt
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295331

CATALOG NUMBER: P3A13R15W2N902750DE010 E3CD1MMS_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1295331

CATALOG NUMBER: P3A13R15W2N902750DE010 E3CD1MMS_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20
RC	80					70					50					30					10
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10
RCR																					
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102
1	116	114	112	111		113	112	110	109		108	107	106		104	103	103		101	100	100
2	113	110	107	105		111	108	106	104		105	103	101		102	101	99		99	98	97
3	110	106	103	100		108	105	102	100		102	100	98		100	98	97		98	97	95
4	107	103	100	97		106	102	99	97		100	97	95		98	96	94		97	95	93
5	105	100	97	94		104	99	96	94		98	95	93		96	94	92		95	93	92
6	103	98	94	92		102	97	94	92		96	93	91		95	92	91		94	92	90
7	101	96	92	90		100	95	92	90		94	91	89		93	91	89		92	90	89
8	99	94	90	88		98	93	90	88		92	90	88		92	89	87		91	89	87
9	97	92	89	87		97	92	89	87		91	88	86		90	88	86		90	87	86
10	96	90	87	85		95	90	87	85		89	87	85		89	86	85		88	86	85

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1897107
5°	1589958
10°	748928
15°	225790
20°	83541
25°	32494
30°	12103
35°	3721
40°	1317
45°	713
50°	512
55°	573
60°	658
65°	415
70°	513
75°	678
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 713 cd/sqm

TEST NUMBER: P1295331

CATALOG NUMBER: P3A13R15W2N902750DE010 E3CD1MMS_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	558.4	57.2
10°-20°	331.9	34.0
20°-30°	69.7	7.1
30°-40°	11.2	1.2
40°-50°	1.9	0.2
50°-60°	1.3	0.1
60°-70°	0.9	0.1
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	960.1	98.4
0°-40°	971.3	99.5
0°-60°	974.6	99.9
0°-90°	976.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	976.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	8652	
5°	7223	558
15°	995	332
25°	134	70
35°	14	11
45°	2	2
55°	2	1
65°	1	1
75°	1	1
85°	0	0
90°	0	

TEST NUMBER: P1295331

CATALOG NUMBER: P3A13R15W2N902750DE010 E3CD1MMS_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	8651.5
1°	8624.5
2°	8487.2
3°	8212.5
4°	7809.7
5°	7223.2
6°	6534.2
7°	5746.3
8°	4994.0
9°	4142.1
10°	3363.5
12.5°	1814.9
15°	994.6
17.5°	582.6
20°	358.0
22.5°	219.1
25°	134.3
27.5°	81.0
30°	47.8
32.5°	27.0
35°	13.9
37.5°	7.7
40°	4.6
42.5°	3.1
45°	2.3
47.5°	1.5
50°	1.5
52.5°	1.5
55°	1.5
57.5°	1.5
60°	1.5
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)