

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297043

Luminaire Tested: P3A13R40W2N902750DE010 E3DLD1GPH\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297043  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R40W2N902750DE010 E3DLD1GPH\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,  
E3DLD1GPH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 334.9 lumens  
Efficiency: N/A  
Efficacy: 27.2 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297043  
CATALOG NUMBER: P3A13R40W2N902750DE010 E3DLD1GPH\_3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1297043

CATALOG NUMBER: P3A13R40W2N902750DE010 E3DLD1GPH\_3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	104	110	107	104	102	103	101	99	99	98	96	96	94	93	91			91
2	106	100	96	92	104	98	94	91	95	92	89	92	89	87	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	85	79	74	92	84	78	74	82	77	73	80	75	72	78	74	71	69			69
5	89	79	73	68	87	78	72	67	76	71	67	75	70	66	73	69	66	64			64
6	84	74	67	62	82	73	67	62	71	66	62	70	65	61	68	64	61	59			59
7	79	69	62	57	78	68	62	57	67	61	57	65	60	57	64	60	56	55			55
8	75	64	58	53	74	64	58	53	63	57	53	62	56	53	61	56	52	51			51
9	71	60	54	50	70	60	54	50	59	53	49	58	53	49	57	52	49	48			48
10	67	57	51	46	66	56	50	46	56	50	46	55	50	46	54	49	46	45			45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	75191
5°	73828
10°	69605
15°	63224
20°	55538
25°	47422
30°	39297
35°	30303
40°	21555
45°	14513
50°	7914
55°	5582
60°	5263
65°	4877
70°	4296
75°	4151
80°	3283
85°	2768

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14513 cd/sqm



TEST NUMBER: P1297043

CATALOG NUMBER: P3A13R40W2N902750DE010 E3DLD1GPH\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	31.3	9.3
10°-20°	77.6	23.2
20°-30°	89.7	26.8
30°-40°	70.7	21.1
40°-50°	36.3	10.8
50°-60°	13.9	4.1
60°-70°	9.2	2.7
70°-80°	5.0	1.5
80°-90°	1.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	198.5	59.3
0°-40°	269.2	80.4
0°-60°	319.3	95.3
0°-90°	334.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	334.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	343	
5°	335	31
15°	278	78
25°	196	90
35°	113	71
45°	47	36
55°	15	14
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1297043  
CATALOG NUMBER: P3A13R40W2N902750DE010 E3DLD1GPH\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	342.9
2.5°	341.1
5°	335.4
7.5°	325.7
10°	312.6
12.5°	297.2
15°	278.5
17.5°	259.0
20°	238.0
22.5°	216.6
25°	196.0
27.5°	175.4
30°	155.2
32.5°	134.6
35°	113.2
37.5°	93.3
40°	75.3
42.5°	60.0
45°	46.8
47.5°	34.1
50°	23.2
52.5°	16.9
55°	14.6
57.5°	13.1
60°	12.0
62.5°	10.5
65°	9.4
67.5°	7.9
70°	6.7
72.5°	5.6
75°	4.9
77.5°	3.7
80°	2.6
82.5°	2.2
85°	1.1
87.5°	0.7
90°	0.0

(END OF REPORT)