

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297198

Luminaire Tested: P3A13R40W2N902765DE010 E3DL1WMH\_2700K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1297198  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R40W2N902765DE010 E3DL1WMH\_2700K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 2700K CCT AND, 90CRI ,  
E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 807.0 lumens  
Efficiency: N/A  
Efficacy: 65.6 lumens/watt  
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297198  
CATALOG NUMBER: P3A13R40W2N902765DE010 E3DL1WMH\_2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P1297198  
 CATALOG NUMBER: P3A13R40W2N902765DE010 E3DL1WMH\_2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	94	94	94	94
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89	89	89	89
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84	84	84	84
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80	80	80	80
5	96	88	83	79	94	88	83	79	86	82	78	84	81	78	83	80	77	76	76	76	76
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72	72	72	72
7	88	80	75	71	87	79	74	71	78	74	71	77	73	70	76	73	70	69	69	69	69
8	85	76	71	68	84	76	71	67	75	70	67	74	70	67	73	69	67	65	65	65	65
9	82	73	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	63	63	63	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	60	60	60	60

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	357099
5°	346708
10°	314623
15°	259933
20°	187500
25°	115966
30°	62794
35°	32444
40°	17633
45°	9892
50°	4947
55°	3708
60°	3333
65°	3217
70°	3077
75°	2965
80°	2652
85°	1761

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9892 cd/sqm



TEST NUMBER: P1297198

CATALOG NUMBER: P3A13R40W2N902765DE010 E3DL1WMH\_2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	145.2	18.0
10°-20°	311.8	38.6
20°-30°	222.5	27.6
30°-40°	81.9	10.2
40°-50°	25.8	3.2
50°-60°	9.0	1.1
60°-70°	6.1	0.8
70°-80°	3.7	0.5
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	679.5	84.2
0°-40°	761.4	94.3
0°-60°	796.1	98.7
0°-90°	807.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	807.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1628	
5°	1575	145
15°	1145	312
25°	479	222
35°	121	82
45°	32	26
55°	10	9
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1297198

CATALOG NUMBER: P3A13R40W2N902765DE010 E3DL1WMH\_2700K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1628.5
2.5°	1616.0
5°	1575.1
7.5°	1507.3
10°	1413.0
12.5°	1293.2
15°	1145.0
17.5°	978.7
20°	803.5
22.5°	631.0
25°	479.3
27.5°	351.9
30°	248.0
32.5°	173.9
35°	121.2
37.5°	85.9
40°	61.6
42.5°	44.3
45°	31.9
47.5°	21.5
50°	14.5
52.5°	10.4
55°	9.7
57.5°	9.0
60°	7.6
62.5°	6.9
65°	6.2
67.5°	5.5
70°	4.8
72.5°	4.2
75°	3.5
77.5°	2.8
80°	2.1
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

(END OF REPORT)