

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297236

Luminaire Tested: P3A13R40W2N902765DE010 E3DLD1WMH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297236
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R40W2N902765DE010 E3DLD1WMH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3500K CCT AND, 90CRI ,
E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 693.0 lumens
Efficiency: N/A
Efficacy: 56.3 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297236

CATALOG NUMBER: P3A13R40W2N902765DE010 E3DLD1WMH_3500K

Luminous Intensity Polar Plot



TEST NUMBER: P1297236

CATALOG NUMBER: P3A13R40W2N902765DE010 E3DLD1WMH_3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	112	109	106	104	110	107	104	102	103	101	99		99	98	96		96	94	93		91
2	106	100	96	92	104	98	94	91	95	92	89		92	89	87		89	87	85		83
3	100	92	87	82	98	91	86	81	88	84	80		86	82	79		83	80	78		76
4	94	85	79	74	92	84	78	74	82	77	73		80	75	72		78	74	71		69
5	89	79	73	68	87	78	72	67	76	71	67		75	70	66		73	69	66		64
6	84	74	67	62	82	73	67	62	71	66	61		70	65	61		68	64	61		59
7	79	69	62	57	78	68	62	57	67	61	57		65	60	57		64	60	56		55
8	75	64	58	53	74	64	57	53	63	57	53		62	56	53		61	56	52		51
9	71	60	54	50	70	60	54	50	59	53	49		58	53	49		57	52	49		48
10	67	57	51	46	66	56	50	46	56	50	46		55	50	46		54	49	46		45

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	155558
5°	152740
10°	143974
15°	130784
20°	114880
25°	98111
30°	81278
35°	62694
40°	44598
45°	30050
50°	16409
55°	11546
60°	10876
65°	10066
70°	8976
75°	8557
80°	6819
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 30050 cd/sqm

TEST NUMBER: P1297236

CATALOG NUMBER: P3A13R40W2N902765DE010 E3DLD1WMH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.7	9.3
10°-20°	160.5	23.2
20°-30°	185.5	26.8
30°-40°	146.2	21.1
40°-50°	75.1	10.8
50°-60°	28.7	4.1
60°-70°	19.0	2.7
70°-80°	10.3	1.5
80°-90°	3.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	410.7	59.3
0°-40°	556.9	80.4
0°-60°	660.6	95.3
0°-90°	693.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	693.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	709	
5°	694	65
15°	576	160
25°	406	186
35°	234	146
45°	97	75
55°	30	29
65°	19	19
75°	10	10
85°	2	3
90°	0	

TEST NUMBER: P1297236

CATALOG NUMBER: P3A13R40W2N902765DE010 E3DLD1WMH_3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	709.4
2.5°	705.6
5°	693.9
7.5°	673.8
10°	646.6
12.5°	614.8
15°	576.1
17.5°	535.8
20°	492.3
22.5°	448.1
25°	405.5
27.5°	362.9
30°	321.0
32.5°	278.3
35°	234.2
37.5°	193.1
40°	155.8
42.5°	124.1
45°	96.9
47.5°	70.6
50°	48.1
52.5°	34.9
55°	30.2
57.5°	27.1
60°	24.8
62.5°	21.7
65°	19.4
67.5°	16.3
70°	14.0
72.5°	11.6
75°	10.1
77.5°	7.8
80°	5.4
82.5°	4.7
85°	2.3
87.5°	1.6
90°	0.0

(END OF REPORT)