

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295530

Luminaire Tested: P3A13R15W2N902765DE010 E3D1WMH\_4000K

Issue Date: 1/29/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1295530  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2501-338-7)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/29/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R15W2N902765DE010 E3D1WMH\_4000K  
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 4000K CCT AND, 90CRI ,  
E3D1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1003.0 lumens  
Efficiency: N/A  
Efficacy: 81.5 lumens/watt  
Spacing Criteria (0/90/45): 0.3 / 0.3 / 0.29  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1295530

CATALOG NUMBER: P3A13R15W2N902765DE010 E3D1WMH\_4000K

### Luminous Intensity Polar Plot



TEST NUMBER: P1295530

CATALOG NUMBER: P3A13R15W2N902765DE010 E3D1WMH\_4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|
| RF  | 20  |     |     |     | 20  |     |     |     |     | 20  |     |     |     |     | 20  |     |     |     |    | 20 |
| RC  | 80  |     |     |     | 70  |     |     |     |     | 50  |     |     |     |     | 30  |     |     |     |    | 10 |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30 | 10 |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |    |    |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 |    |    |
| 1   | 116 | 114 | 112 | 111 | 113 | 112 | 110 | 109 | 108 | 107 | 105 | 104 | 103 | 102 | 101 | 100 | 99  | 98  |    |    |
| 2   | 112 | 109 | 107 | 105 | 110 | 108 | 105 | 103 | 105 | 103 | 101 | 102 | 100 | 99  | 99  | 98  | 97  | 96  |    |    |
| 3   | 110 | 106 | 102 | 100 | 108 | 104 | 102 | 99  | 102 | 100 | 98  | 100 | 98  | 96  | 98  | 96  | 95  | 94  |    |    |
| 4   | 107 | 102 | 99  | 96  | 106 | 101 | 98  | 96  | 99  | 97  | 95  | 98  | 96  | 94  | 96  | 94  | 93  | 92  |    |    |
| 5   | 105 | 100 | 96  | 94  | 103 | 99  | 96  | 93  | 97  | 94  | 92  | 96  | 93  | 92  | 94  | 93  | 91  | 90  |    |    |
| 6   | 102 | 97  | 94  | 91  | 101 | 96  | 93  | 91  | 95  | 92  | 90  | 94  | 92  | 90  | 93  | 91  | 89  | 88  |    |    |
| 7   | 100 | 95  | 91  | 89  | 99  | 94  | 91  | 89  | 93  | 90  | 88  | 92  | 90  | 88  | 91  | 89  | 88  | 87  |    |    |
| 8   | 98  | 93  | 89  | 87  | 97  | 92  | 89  | 87  | 91  | 89  | 87  | 91  | 88  | 86  | 90  | 88  | 86  | 85  |    |    |
| 9   | 96  | 91  | 88  | 85  | 96  | 91  | 87  | 85  | 90  | 87  | 85  | 89  | 87  | 85  | 89  | 86  | 85  | 84  |    |    |
| 10  | 95  | 89  | 86  | 84  | 94  | 89  | 86  | 84  | 88  | 85  | 83  | 88  | 85  | 83  | 87  | 85  | 83  | 82  |    |    |

**AVERAGE LUMINANCE (cd/sqm):**

|     |         |
|-----|---------|
|     | 0°      |
| 0°  | 1909979 |
| 5°  | 1557447 |
| 10° | 762756  |
| 15° | 233463  |
| 20° | 98872   |
| 25° | 44712   |
| 30° | 17420   |
| 35° | 8031    |
| 40° | 2490    |
| 45° | 930     |
| 50° | 375     |
| 55° | 153     |
| 60° | 175     |
| 65° | 208     |
| 70° | 0       |
| 75° | 0       |
| 80° | 0       |
| 85° | 0       |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 930 cd/sqm

TEST NUMBER: P1295530

CATALOG NUMBER: P3A13R15W2N902765DE010 E3D1WMH\_4000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 550.7  | 54.9      |
| 10°-20°   | 337.9  | 33.7      |
| 20°-30°   | 90.8   | 9.0       |
| 30°-40°   | 20.0   | 2.0       |
| 40°-50°   | 2.8    | 0.3       |
| 50°-60°   | 0.5    | 0.1       |
| 60°-70°   | 0.2    | 0.0       |
| 70°-80°   | 0.0    | 0.0       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 979.5  | 97.7      |
| 0°-40°    | 999.4  | 99.6      |
| 0°-60°    | 1002.7 | 100.0     |
| 0°-90°    | 1003.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1003.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 8710 |      |
| 5°  | 7076 | 551  |
| 15° | 1028 | 338  |
| 25° | 185  | 91   |
| 35° | 30   | 20   |
| 45° | 3    | 3    |
| 55° | 0    | 1    |
| 65° | 0    | 0    |
| 75° | 0    | 0    |
| 85° | 0    | 0    |
| 90° | 0    |      |

TEST NUMBER: P1295530

CATALOG NUMBER: P3A13R15W2N902765DE010 E3D1WMH\_4000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 8710.2 |
| 1°    | 8655.8 |
| 2°    | 8481.2 |
| 3°    | 8166.7 |
| 4°    | 7693.2 |
| 5°    | 7075.5 |
| 6°    | 6376.9 |
| 7°    | 5598.7 |
| 8°    | 4883.7 |
| 9°    | 4125.7 |
| 10°   | 3425.6 |
| 11°   | 2732.6 |
| 12°   | 2102.4 |
| 13°   | 1617.1 |
| 14°   | 1280.2 |
| 15°   | 1028.4 |
| 17.5° | 637.4  |
| 20°   | 423.7  |
| 22.5° | 285.2  |
| 25°   | 184.8  |
| 27.5° | 109.5  |
| 30°   | 68.8   |
| 32.5° | 46.4   |
| 35°   | 30.0   |
| 37.5° | 16.7   |
| 40°   | 8.7    |
| 42.5° | 4.9    |
| 45°   | 3.0    |
| 47.5° | 1.9    |
| 50°   | 1.1    |
| 52.5° | 0.8    |
| 55°   | 0.4    |
| 57.5° | 0.4    |
| 60°   | 0.4    |
| 62.5° | 0.4    |
| 65°   | 0.4    |
| 67.5° | 0.0    |
| 70°   | 0.0    |
| 72.5° | 0.0    |
| 75°   | 0.0    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |



TEST NUMBER: P1295530

CATALOG NUMBER: P3A13R15W2N902765DE010 E3D1WMH\_4000K

CANDELA DISTRIBUTION (continued):

0°  
90° | 0.0

(END OF REPORT)