

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297311

Luminaire Tested: P3A13R45W2N902750DE010 E3DL1GPH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297311
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R45W2N902750DE010 E3DL1GPH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 380.0 lumens
Efficiency: N/A
Efficacy: 30.9 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297311

CATALOG NUMBER: P3A13R45W2N902750DE010 E3DL1GPH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1297311

CATALOG NUMBER: P3A13R45W2N902750DE010 E3DL1GPH_2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	114	111	109	107		111	109	107	105		105	103	102		101	100	99		98	97	96		94			
2	109	104	100	97		106	102	99	96		99	96	94		96	94	92		93	91	90		88			
3	104	98	93	89		102	96	92	88		94	90	87		91	88	86		89	86	84		83			
4	99	92	87	83		97	91	86	82		89	85	81		87	83	80		85	82	79		78			
5	94	87	81	77		93	86	81	77		84	80	76		82	79	76		81	78	75		74			
6	90	82	76	73		89	81	76	72		80	75	72		78	74	71		77	74	71		70			
7	86	78	72	68		85	77	72	68		76	71	68		75	71	67		74	70	67		66			
8	83	74	68	65		82	73	68	64		72	68	64		71	67	64		70	67	64		62			
9	79	70	65	61		78	70	65	61		69	64	61		68	64	61		67	63	61		59			
10	76	67	62	58		75	67	62	58		66	61	58		65	61	58		65	61	58		57			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	142708
5°	139357
10°	128098
15°	108536
20°	84217
25°	58866
30°	37094
35°	21844
40°	12366
45°	6016
50°	2081
55°	1682
60°	1623
65°	1608
70°	1539
75°	1440
80°	1263
85°	755

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6016 cd/sqm

TEST NUMBER: P1297311

CATALOG NUMBER: P3A13R45W2N902750DE010 E3DL1GPH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	15.4
10°-20°	131.3	34.5
20°-30°	111.5	29.3
30°-40°	53.2	14.0
40°-50°	16.0	4.2
50°-60°	4.1	1.1
60°-70°	3.0	0.8
70°-80°	1.8	0.5
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	301.4	79.3
0°-40°	354.6	93.3
0°-60°	374.7	98.6
0°-90°	380.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	380.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	651	
5°	633	59
15°	478	131
25°	243	112
35°	82	53
45°	19	16
55°	4	4
65°	3	3
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P1297311

CATALOG NUMBER: P3A13R45W2N902750DE010 E3DL1GPH_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	650.8
2.5°	646.7
5°	633.1
7.5°	609.7
10°	575.3
12.5°	529.8
15°	478.1
17.5°	420.7
20°	360.9
22.5°	300.1
25°	243.3
27.5°	191.7
30°	146.5
32.5°	110.1
35°	81.6
37.5°	60.2
40°	43.2
42.5°	29.9
45°	19.4
47.5°	10.9
50°	6.1
52.5°	4.8
55°	4.4
57.5°	4.1
60°	3.7
62.5°	3.4
65°	3.1
67.5°	2.7
70°	2.4
72.5°	2.0
75°	1.7
77.5°	1.4
80°	1.0
82.5°	0.7
85°	0.3
87.5°	0.3
90°	0.0

(END OF REPORT)