

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295639

Luminaire Tested: P3A13R15W2N902765DE010 E3DLP1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295639
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-1)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R15W2N902765DE010 E3DLP1WMH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 5000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 475.0 lumens
Efficiency: N/A
Efficacy: 38.6 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.61
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295639

CATALOG NUMBER: P3A13R15W2N902765DE010 E3DLP1WMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1295639

CATALOG NUMBER: P3A13R15W2N902765DE010 E3DLP1WMH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	113	110	108	106		111	108	106	104		104	102	101		100	99	98		97	96	95		93			
2	108	103	98	95		105	101	97	94		98	95	92		95	92	90		92	90	88		86			
3	102	96	91	87		100	94	90	86		92	88	85		89	86	83		87	84	82		80			
4	97	90	84	80		95	88	83	79		86	82	78		84	81	78		82	79	77		75			
5	93	84	78	74		91	83	78	74		81	77	73		80	76	72		78	75	72		70			
6	88	79	73	69		87	79	73	69		77	72	69		76	71	68		74	71	68		66			
7	84	75	69	65		83	74	69	65		73	68	64		72	67	64		71	67	64		62			
8	80	71	65	61		79	71	65	61		69	64	61		68	64	61		67	63	60		59			
9	77	68	62	58		76	67	62	58		66	61	58		65	61	57		64	60	57		56			
10	74	64	59	55		73	64	59	55		63	58	55		62	58	55		62	57	54		53			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	204830
5°	189324
10°	151144
15°	114166
20°	86948
25°	66246
30°	47450
35°	30972
40°	18978
45°	11474
50°	7642
55°	5887
60°	5087
65°	4410
70°	3975
75°	3897
80°	2904
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 11474 cd/sqm

TEST NUMBER: P1295639

CATALOG NUMBER: P3A13R15W2N902765DE010 E3DLP1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.2	16.0
10°-20°	140.6	29.6
20°-30°	125.1	26.3
30°-40°	74.0	15.6
40°-50°	30.4	6.4
50°-60°	14.3	3.0
60°-70°	8.7	1.8
70°-80°	4.6	1.0
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	341.9	72.0
0°-40°	415.9	87.6
0°-60°	460.6	97.0
0°-90°	475.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	475.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	934	
5°	860	76
15°	503	141
25°	274	125
35°	116	74
45°	37	30
55°	15	14
65°	8	9
75°	5	5
85°	1	1
90°	0	

TEST NUMBER: P1295639

CATALOG NUMBER: P3A13R15W2N902765DE010 E3DLP1WMH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	934.1
1°	931.8
2°	924.8
3°	911.0
4°	887.8
5°	860.1
6°	830.0
7°	794.5
8°	757.5
9°	719.7
10°	678.8
12.5°	585.5
15°	502.9
17.5°	432.0
20°	372.6
22.5°	320.1
25°	273.8
27.5°	229.1
30°	187.4
32.5°	149.6
35°	115.7
37.5°	88.7
40°	66.3
42.5°	49.4
45°	37.0
47.5°	28.5
50°	22.4
52.5°	18.5
55°	15.4
57.5°	13.1
60°	11.6
62.5°	10.0
65°	8.5
67.5°	7.7
70°	6.2
72.5°	5.4
75°	4.6
77.5°	3.1
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)