

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297712

Luminaire Tested: P3A13R50W2N902765DE010 E3CB1MW_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297712
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R50W2N902765DE010 E3CB1MW_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 5000K CCT AND, 90CRI ,
E3CB1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1056.0 lumens
Efficiency: N/A
Efficacy: 85.9 lumens/watt
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297712

CATALOG NUMBER: P3A13R50W2N902765DE010 E3CB1MW_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297712

CATALOG NUMBER: P3A13R50W2N902765DE010 E3CB1MW_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10		70	50	30	10		50	30	10		50	30	10		50	30	10		0			
RCR																										
0	119	119	119	119		116	116	116	116		111	111	111		106	106	106		102	102	102		100			
1	114	112	109	107		112	109	107	106		105	104	102		102	101	99		98	97	96		95			
2	109	105	101	98		107	103	100	97		100	97	95		97	95	93		94	93	91		90			
3	105	99	95	91		103	98	94	90		95	92	89		93	90	88		91	88	86		85			
4	100	94	89	85		99	92	88	85		90	87	84		88	85	83		87	84	82		80			
5	96	89	84	80		94	88	83	79		86	82	79		84	81	78		83	80	77		76			
6	92	84	79	75		91	83	79	75		82	78	74		81	77	74		79	76	73		72			
7	88	80	75	71		87	79	74	71		78	74	71		77	73	70		76	73	70		69			
8	85	76	71	67		83	76	71	67		75	70	67		74	70	67		73	69	66		65			
9	81	73	68	64		80	72	67	64		71	67	64		71	66	63		70	66	63		62			
10	78	69	64	61		77	69	64	61		68	64	61		68	63	61		67	63	60		59			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	367778
5°	361192
10°	346798
15°	318027
20°	280421
25°	214948
30°	116879
35°	37611
40°	8845
45°	1209
50°	1058
55°	1185
60°	1009
65°	1193
70°	962
75°	1271
80°	1010
85°	2013

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 85°

Luminance: 2013 cd/sqm

TEST NUMBER: P1297712

CATALOG NUMBER: P3A13R50W2N902765DE010 E3CB1MW_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.0	14.6
10°-20°	389.4	36.9
20°-30°	390.0	36.9
30°-40°	109.7	10.4
40°-50°	6.6	0.6
50°-60°	2.5	0.2
60°-70°	2.0	0.2
70°-80°	1.3	0.1
80°-90°	0.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	933.4	88.4
0°-40°	1043.1	98.8
0°-60°	1052.2	99.6
0°-90°	1056.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1056.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1677	
5°	1641	154
15°	1401	389
25°	888	390
35°	140	110
45°	4	7
55°	3	3
65°	2	2
75°	2	1
85°	1	1
90°	0	

TEST NUMBER: P1297712

CATALOG NUMBER: P3A13R50W2N902765DE010 E3CB1MW_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1677.2
2.5°	1668.7
5°	1640.9
7.5°	1603.1
10°	1557.5
12.5°	1488.9
15°	1400.9
17.5°	1299.8
20°	1201.7
22.5°	1079.8
25°	888.4
27.5°	661.5
30°	461.6
32.5°	278.6
35°	140.5
37.5°	66.4
40°	30.9
42.5°	11.6
45°	3.9
47.5°	3.1
50°	3.1
52.5°	3.1
55°	3.1
57.5°	2.3
60°	2.3
62.5°	2.3
65°	2.3
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.8
87.5°	0.0
90°	0.0

(END OF REPORT)