

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297713

Luminaire Tested: P3A13R50W2N902765DE010 E3CB1MW\_6500K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1297713  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-32)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R50W2N902765DE010 E3CB1MW\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 6500K CCT AND, 90CRI ,  
E3CB1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 1056.0 lumens  
Efficiency: N/A  
Efficacy: 85.9 lumens/watt  
Spacing Criteria (0/90/45): 0.84 / 0.84 / 0.76  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297713

CATALOG NUMBER: P3A13R50W2N902765DE010 E3CB1MW\_6500K

### Luminous Intensity Polar Plot





TEST NUMBER: P1297713

CATALOG NUMBER: P3A13R50W2N902765DE010 E3CB1MW\_6500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
|-----|-----|-----|-----|-----|--|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|
| RF  | 20  |     |     |     |  | 20  |     |     |     |  | 20  |     |     |  |     | 20  |     |  |     |     | 20  |
| RC  | 80  |     |     |     |  | 70  |     |     |     |  | 50  |     |     |  |     | 30  |     |  |     |     | 10  |
| RW  | 70  | 50  | 30  | 10  |  | 70  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  | 30  | 10  |
| RCR |     |     |     |     |  |     |     |     |     |  |     |     |     |  |     |     |     |  |     |     |     |
| 0   | 119 | 119 | 119 | 119 |  | 116 | 116 | 116 | 116 |  | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 | 102 | 102 |
| 1   | 114 | 112 | 109 | 107 |  | 112 | 109 | 107 | 106 |  | 105 | 104 | 102 |  | 102 | 101 | 99  |  | 98  | 97  | 96  |
| 2   | 109 | 105 | 101 | 98  |  | 107 | 103 | 100 | 97  |  | 100 | 97  | 95  |  | 97  | 95  | 93  |  | 94  | 93  | 91  |
| 3   | 105 | 99  | 95  | 91  |  | 103 | 98  | 94  | 90  |  | 95  | 92  | 89  |  | 93  | 90  | 88  |  | 91  | 88  | 86  |
| 4   | 100 | 94  | 89  | 85  |  | 99  | 92  | 88  | 85  |  | 90  | 87  | 84  |  | 88  | 85  | 83  |  | 87  | 84  | 82  |
| 5   | 96  | 89  | 84  | 80  |  | 94  | 88  | 83  | 79  |  | 86  | 82  | 79  |  | 84  | 81  | 78  |  | 83  | 80  | 77  |
| 6   | 92  | 84  | 79  | 75  |  | 91  | 83  | 79  | 75  |  | 82  | 78  | 74  |  | 81  | 77  | 74  |  | 79  | 76  | 73  |
| 7   | 88  | 80  | 75  | 71  |  | 87  | 79  | 74  | 71  |  | 78  | 74  | 71  |  | 77  | 73  | 70  |  | 76  | 73  | 70  |
| 8   | 85  | 76  | 71  | 67  |  | 83  | 76  | 71  | 67  |  | 75  | 70  | 67  |  | 74  | 70  | 67  |  | 73  | 69  | 66  |
| 9   | 81  | 73  | 68  | 64  |  | 80  | 72  | 67  | 64  |  | 71  | 67  | 64  |  | 71  | 66  | 63  |  | 70  | 66  | 63  |
| 10  | 78  | 69  | 64  | 61  |  | 77  | 69  | 64  | 61  |  | 68  | 64  | 61  |  | 68  | 63  | 61  |  | 67  | 63  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 367778 |
| 5°  | 361192 |
| 10° | 346798 |
| 15° | 318027 |
| 20° | 280421 |
| 25° | 214948 |
| 30° | 116879 |
| 35° | 37611  |
| 40° | 8845   |
| 45° | 1209   |
| 50° | 1058   |
| 55° | 1185   |
| 60° | 1009   |
| 65° | 1193   |
| 70° | 962    |
| 75° | 1271   |
| 80° | 1010   |
| 85° | 2013   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 85°  
Luminance: 2013 cd/sqm

TEST NUMBER: P1297713

CATALOG NUMBER: P3A13R50W2N902765DE010 E3CB1MW\_6500K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 154.0  | 14.6      |
| 10°-20°   | 389.4  | 36.9      |
| 20°-30°   | 390.0  | 36.9      |
| 30°-40°   | 109.7  | 10.4      |
| 40°-50°   | 6.6    | 0.6       |
| 50°-60°   | 2.5    | 0.2       |
| 60°-70°   | 2.0    | 0.2       |
| 70°-80°   | 1.3    | 0.1       |
| 80°-90°   | 0.5    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 933.4  | 88.4      |
| 0°-40°    | 1043.1 | 98.8      |
| 0°-60°    | 1052.2 | 99.6      |
| 0°-90°    | 1056.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 1056.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1677 |      |
| 5°  | 1641 | 154  |
| 15° | 1401 | 389  |
| 25° | 888  | 390  |
| 35° | 140  | 110  |
| 45° | 4    | 7    |
| 55° | 3    | 3    |
| 65° | 2    | 2    |
| 75° | 2    | 1    |
| 85° | 1    | 1    |
| 90° | 0    |      |



TEST NUMBER: P1297713

CATALOG NUMBER: P3A13R50W2N902765DE010 E3CB1MW\_6500K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1677.2 |
| 2.5°  | 1668.7 |
| 5°    | 1640.9 |
| 7.5°  | 1603.1 |
| 10°   | 1557.5 |
| 12.5° | 1488.9 |
| 15°   | 1400.9 |
| 17.5° | 1299.8 |
| 20°   | 1201.7 |
| 22.5° | 1079.8 |
| 25°   | 888.4  |
| 27.5° | 661.5  |
| 30°   | 461.6  |
| 32.5° | 278.6  |
| 35°   | 140.5  |
| 37.5° | 66.4   |
| 40°   | 30.9   |
| 42.5° | 11.6   |
| 45°   | 3.9    |
| 47.5° | 3.1    |
| 50°   | 3.1    |
| 52.5° | 3.1    |
| 55°   | 3.1    |
| 57.5° | 2.3    |
| 60°   | 2.3    |
| 62.5° | 2.3    |
| 65°   | 2.3    |
| 67.5° | 1.5    |
| 70°   | 1.5    |
| 72.5° | 1.5    |
| 75°   | 1.5    |
| 77.5° | 0.8    |
| 80°   | 0.8    |
| 82.5° | 0.8    |
| 85°   | 0.8    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)