

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295750

Luminaire Tested: P3A13R20W2N902750DE010 E3DLD1LI\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1295750  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R20W2N902750DE010 E3DLD1LI\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,  
E3DLD1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 602.0 lumens  
Efficiency: N/A  
Efficacy: 48.9 lumens/watt  
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1295750  
CATALOG NUMBER: P3A13R20W2N902750DE010 E3DLD1LI\_3000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1295750  
 CATALOG NUMBER: P3A13R20W2N902750DE010 E3DLD1LI\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	60.9	10.1
10°-20°	143.9	23.9
20°-30°	159.7	26.5
30°-40°	121.9	20.2
40°-50°	62.4	10.4
50°-60°	25.6	4.3
60°-70°	16.0	2.7
70°-80°	9.0	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.6	60.6
0°-40°	486.4	80.8
0°-60°	574.4	95.4
0°-90°	602.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	602.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	679	
5°	658	61
15°	517	144
25°	350	160
35°	194	122
45°	79	62
55°	26	26
65°	16	16
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1295750  
CATALOG NUMBER: P3A13R20W2N902750DE010 E3DLD1LI\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	679.1
1°	679.8
2°	676.8
3°	672.9
4°	666.8
5°	658.4
6°	648.5
7°	637.8
8°	626.3
9°	612.5
10°	598.8
12.5°	559.0
15°	516.9
17.5°	474.1
20°	431.3
22.5°	388.5
25°	349.5
27.5°	310.5
30°	269.9
32.5°	231.7
35°	194.2
37.5°	161.4
40°	129.2
42.5°	101.7
45°	78.8
47.5°	59.6
50°	44.4
52.5°	32.9
55°	26.0
57.5°	23.7
60°	20.6
62.5°	18.4
65°	16.1
67.5°	13.8
70°	12.2
72.5°	9.9
75°	8.4
77.5°	6.9
80°	5.4
82.5°	3.8
85°	2.3
87.5°	0.8
90°	0.0

(END OF REPORT)