

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297876

Luminaire Tested: P3A13R55W2N902750DE010 E3CB1MMS_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297876
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-36)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R55W2N902750DE010 E3CB1MMS_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,
E3CB1MMS TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 1017.0 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297876

CATALOG NUMBER: P3A13R55W2N902750DE010 E3CB1MMS_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297876

CATALOG NUMBER: P3A13R55W2N902750DE010 E3CB1MMS_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	107	112	109	107	105	105	104	102	101	100	99	98	97	96	94		
2	109	104	101	98	107	103	99	96	100	97	94	97	94	92	94	92	90	89		
3	104	98	94	90	102	97	93	89	94	91	88	92	89	86	90	87	85	84		
4	99	92	87	84	98	91	87	83	89	85	82	87	84	81	85	83	80	79		
5	95	87	82	78	93	86	81	78	85	80	77	83	79	76	82	78	76	74		
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	72	70		
7	87	78	73	69	85	78	72	69	76	72	68	75	71	68	74	70	68	66		
8	83	74	69	65	82	74	68	65	73	68	65	72	67	64	71	67	64	63		
9	79	71	65	61	78	70	65	61	69	64	61	68	64	61	68	64	61	60		
10	76	67	62	58	75	67	62	58	66	61	58	65	61	58	65	61	58	57		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	282061
5°	279440
10°	290687
15°	286630
20°	264320
25°	215069
30°	130628
35°	45213
40°	12910
45°	6171
50°	2593
55°	1185
60°	1360
65°	1193
70°	962
75°	1271
80°	1010
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 6171 cd/sqm

TEST NUMBER: P1297876

CATALOG NUMBER: P3A13R55W2N902750DE010 E3CB1MMS_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	12.1
10°-20°	350.9	34.5
20°-30°	391.2	38.5
30°-40°	128.0	12.6
40°-50°	16.9	1.7
50°-60°	3.6	0.4
60°-70°	2.1	0.2
70°-80°	1.3	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	864.9	85.0
0°-40°	992.8	97.6
0°-60°	1013.3	99.6
0°-90°	1017.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1017.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1286	
5°	1270	123
15°	1263	351
25°	889	391
35°	169	128
45°	20	17
55°	3	4
65°	2	2
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P1297876

CATALOG NUMBER: P3A13R55W2N902750DE010 E3CB1MMS_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1286.3
2.5°	1277.2
5°	1269.5
7.5°	1287.9
10°	1305.5
12.5°	1296.3
15°	1262.6
17.5°	1209.1
20°	1132.7
22.5°	1027.2
25°	888.9
27.5°	713.1
30°	515.9
32.5°	316.4
35°	168.9
37.5°	85.6
40°	45.1
42.5°	29.0
45°	19.9
47.5°	13.8
50°	7.6
52.5°	4.6
55°	3.1
57.5°	3.1
60°	3.1
62.5°	2.3
65°	2.3
67.5°	1.5
70°	1.5
72.5°	1.5
75°	1.5
77.5°	0.8
80°	0.8
82.5°	0.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)