

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297954

Luminaire Tested: P3A13R55W2N902750DE010 E3DL1WMH\_5000K

Issue Date: 1/30/2026

**Test Information**

Test Method: LM-79-2019  
Report Number: P1297954  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3A13R55W2N902750DE010 E3DL1WMH\_5000K  
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 90CRI ,  
E3DL1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 841.0 lumens  
Efficiency: N/A  
Efficacy: 68.4 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct

Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1297954

CATALOG NUMBER: P3A13R55W2N902750DE010 E3DL1WMH\_5000K

### Luminous Intensity Polar Plot





TEST NUMBER: P1297954

CATALOG NUMBER: P3A13R55W2N902750DE010 E3DL1WMH\_5000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |  | 20  |     |     |  | 20  |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |  | 30  |     |     |  | 10  |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  |  | 50  | 30  | 10  |  | 50  |
| RCR |     |     |     |     |     |     |     |     |     |     |     |  |     |     |     |  |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 |  | 106 | 106 | 106 |  | 102 |
| 1   | 113 | 111 | 108 | 106 | 111 | 108 | 106 | 104 | 104 | 103 | 101 |  | 101 | 99  | 98  |  | 97  |
| 2   | 108 | 103 | 99  | 95  | 106 | 101 | 97  | 94  | 98  | 95  | 92  |  | 95  | 92  | 90  |  | 92  |
| 3   | 102 | 96  | 91  | 87  | 100 | 94  | 90  | 86  | 92  | 88  | 85  |  | 89  | 86  | 83  |  | 87  |
| 4   | 97  | 90  | 84  | 80  | 95  | 89  | 83  | 79  | 86  | 82  | 78  |  | 84  | 81  | 78  |  | 82  |
| 5   | 92  | 84  | 78  | 74  | 91  | 83  | 78  | 74  | 81  | 77  | 73  |  | 80  | 76  | 72  |  | 78  |
| 6   | 88  | 79  | 73  | 69  | 86  | 78  | 73  | 68  | 77  | 72  | 68  |  | 75  | 71  | 68  |  | 74  |
| 7   | 84  | 74  | 68  | 64  | 82  | 74  | 68  | 64  | 72  | 67  | 64  |  | 71  | 67  | 63  |  | 70  |
| 8   | 80  | 70  | 64  | 60  | 78  | 70  | 64  | 60  | 69  | 63  | 60  |  | 67  | 63  | 60  |  | 67  |
| 9   | 76  | 66  | 61  | 57  | 75  | 66  | 60  | 56  | 65  | 60  | 56  |  | 64  | 59  | 56  |  | 63  |
| 10  | 73  | 63  | 57  | 53  | 72  | 62  | 57  | 53  | 62  | 57  | 53  |  | 61  | 56  | 53  |  | 60  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 230924 |
| 5°  | 228593 |
| 10° | 220749 |
| 15° | 204042 |
| 20° | 176089 |
| 25° | 139073 |
| 30° | 98648  |
| 35° | 63604  |
| 40° | 38214  |
| 45° | 21522  |
| 50° | 11565  |
| 55° | 4129   |
| 60° | 3728   |
| 65° | 3580   |
| 70° | 3462   |
| 75° | 3304   |
| 80° | 2904   |
| 85° | 2013   |

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
Vertical Angle: 45°  
Luminance: 21522 cd/sqm

TEST NUMBER: P1297954

CATALOG NUMBER: P3A13R55W2N902750DE010 E3DL1WMH\_5000K

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 97.7   | 11.6      |
| 10°-20°   | 248.6  | 29.6      |
| 20°-30°   | 260.5  | 31.0      |
| 30°-40°   | 151.9  | 18.1      |
| 40°-50°   | 56.9   | 6.8       |
| 50°-60°   | 13.4   | 1.6       |
| 60°-70°   | 6.9    | 0.8       |
| 70°-80°   | 4.1    | 0.5       |
| 80°-90°   | 1.2    | 0.1       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| <hr/>     |        |           |
| 0°-30°    | 606.7  | 72.1      |
| 0°-40°    | 758.6  | 90.2      |
| 0°-60°    | 828.9  | 98.6      |
| 0°-90°    | 841.0  | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 841.0  | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 1053 |      |
| 5°  | 1038 | 98   |
| 15° | 899  | 249  |
| 25° | 575  | 260  |
| 35° | 238  | 152  |
| 45° | 69   | 57   |
| 55° | 11   | 13   |
| 65° | 7    | 7    |
| 75° | 4    | 4    |
| 85° | 1    | 1    |
| 90° | 0    |      |

TEST NUMBER: P1297954

CATALOG NUMBER: P3A13R55W2N902750DE010 E3DL1WMH\_5000K

**CANDELA DISTRIBUTION (FULL):**

| 0°    |        |
|-------|--------|
| 0°    | 1053.1 |
| 2.5°  | 1050.0 |
| 5°    | 1038.5 |
| 7.5°  | 1020.0 |
| 10°   | 991.4  |
| 12.5° | 951.3  |
| 15°   | 898.8  |
| 17.5° | 832.5  |
| 20°   | 754.6  |
| 22.5° | 667.4  |
| 25°   | 574.8  |
| 27.5° | 479.9  |
| 30°   | 389.6  |
| 32.5° | 307.8  |
| 35°   | 237.6  |
| 37.5° | 180.5  |
| 40°   | 133.5  |
| 42.5° | 95.7   |
| 45°   | 69.4   |
| 47.5° | 50.1   |
| 50°   | 33.9   |
| 52.5° | 19.3   |
| 55°   | 10.8   |
| 57.5° | 9.3    |
| 60°   | 8.5    |
| 62.5° | 7.7    |
| 65°   | 6.9    |
| 67.5° | 6.2    |
| 70°   | 5.4    |
| 72.5° | 4.6    |
| 75°   | 3.9    |
| 77.5° | 3.1    |
| 80°   | 2.3    |
| 82.5° | 1.5    |
| 85°   | 0.8    |
| 87.5° | 0.8    |
| 90°   | 0.0    |

(END OF REPORT)