

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295904

Luminaire Tested: P3A13R20W2N902765DE010 E3DLD1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295904
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R20W2N902765DE010 E3DLD1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 3000K CCT AND, 90CRI ,
E3DLD1MW TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 602.0 lumens
Efficiency: N/A
Efficacy: 48.9 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295904

CATALOG NUMBER: P3A13R20W2N902765DE010 E3DLD1MW_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1295904

CATALOG NUMBER: P3A13R20W2N902765DE010 E3DLD1MW_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102
1	113	109	106	104	110	107	105	102	103	101	99		99	98	96		96
2	106	100	96	92	104	99	94	91	95	92	89		92	89	87		90
3	100	93	87	82	98	91	86	82	88	84	80		86	82	79		84
4	94	86	79	75	92	85	79	74	82	77	73		80	76	72		78
5	89	80	73	68	87	79	73	68	77	71	67		75	70	67		73
6	84	74	68	63	82	73	67	63	72	66	62		70	65	62		69
7	80	69	63	58	78	69	62	58	67	62	58		66	61	57		65
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61
9	72	61	55	50	70	61	55	50	60	54	50		59	54	50		58
10	68	58	51	47	67	57	51	47	56	51	47		56	50	47		55

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	148914
5°	144926
10°	133331
15°	117345
20°	100645
25°	84561
30°	68340
35°	51986
40°	36984
45°	24437
50°	15147
55°	9940
60°	9034
65°	8354
70°	7822
75°	7117
80°	6819
85°	5787

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 24437 cd/sqm

TEST NUMBER: P1295904

CATALOG NUMBER: P3A13R20W2N902765DE010 E3DLD1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	60.9	10.1
10°-20°	143.9	23.9
20°-30°	159.7	26.5
30°-40°	121.9	20.2
40°-50°	62.4	10.4
50°-60°	25.6	4.3
60°-70°	16.0	2.7
70°-80°	9.0	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	364.6	60.6
0°-40°	486.4	80.8
0°-60°	574.4	95.4
0°-90°	602.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	602.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	679	
5°	658	61
15°	517	144
25°	350	160
35°	194	122
45°	79	62
55°	26	26
65°	16	16
75°	8	9
85°	2	3
90°	0	

TEST NUMBER: P1295904

CATALOG NUMBER: P3A13R20W2N902765DE010 E3DLD1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	679.1
1°	679.8
2°	676.8
3°	672.9
4°	666.8
5°	658.4
6°	648.5
7°	637.8
8°	626.3
9°	612.5
10°	598.8
12.5°	559.0
15°	516.9
17.5°	474.1
20°	431.3
22.5°	388.5
25°	349.5
27.5°	310.5
30°	269.9
32.5°	231.7
35°	194.2
37.5°	161.4
40°	129.2
42.5°	101.7
45°	78.8
47.5°	59.6
50°	44.4
52.5°	32.9
55°	26.0
57.5°	23.7
60°	20.6
62.5°	18.4
65°	16.1
67.5°	13.8
70°	12.2
72.5°	9.9
75°	8.4
77.5°	6.9
80°	5.4
82.5°	3.8
85°	2.3
87.5°	0.8
90°	0.0

(END OF REPORT)