

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298121

Luminaire Tested: P3A13R55W2N902765DE010 E3DLD1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298121
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-34)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R55W2N902765DE010 E3DLD1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 90CRI ,
E3DLD1GPH TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 320.0 lumens
Efficiency: N/A
Efficacy: 26.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.97
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298121

CATALOG NUMBER: P3A13R55W2N902765DE010 E3DLD1GPH_5000K

Luminous Intensity Polar Plot



TEST NUMBER: P1298121

CATALOG NUMBER: P3A13R55W2N902765DE010 E3DLD1GPH_5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	112	109	106	103	110	107	104	102	103	100	98		99	97	95		95	94	93		91
2	105	100	95	91	103	98	93	90	94	91	88		91	88	86		89	86	84		82
3	99	91	85	81	97	90	84	80	87	82	79		85	81	77		82	79	76		74
4	93	84	77	72	91	83	77	72	80	75	71		78	74	70		76	73	69		68
5	87	77	71	66	85	76	70	65	75	69	65		73	68	64		71	67	64		62
6	82	72	65	60	80	71	64	60	69	64	59		68	63	59		66	62	58		57
7	77	67	60	55	76	66	59	55	65	59	54		63	58	54		62	57	54		52
8	73	62	55	51	72	62	55	51	60	55	50		59	54	50		58	53	50		48
9	69	58	51	47	68	58	51	47	57	51	47		56	50	46		55	50	46		45
10	65	55	48	44	64	54	48	44	53	47	43		52	47	43		52	47	43		42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	60171
5°	59410
10°	57046
15°	53371
20°	48678
25°	43430
30°	37981
35°	31561
40°	24875
45°	16870
50°	10302
55°	5352
60°	4956
65°	4722
70°	4360
75°	3813
80°	3788
85°	2768

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 16870 cd/sqm

TEST NUMBER: P1298121

CATALOG NUMBER: P3A13R55W2N902765DE010 E3DLD1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.3	7.9
10°-20°	65.7	20.5
20°-30°	82.3	25.7
30°-40°	73.4	22.9
40°-50°	43.0	13.4
50°-60°	14.9	4.6
60°-70°	9.0	2.8
70°-80°	5.0	1.6
80°-90°	1.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	173.3	54.2
0°-40°	246.7	77.1
0°-60°	304.6	95.2
0°-90°	320.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	320.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	274	
5°	270	25
15°	235	66
25°	180	82
35°	118	73
45°	54	43
55°	14	15
65°	9	9
75°	4	5
85°	1	1
90°	0	



TEST NUMBER: P1298121

CATALOG NUMBER: P3A13R55W2N902765DE010 E3DLD1GPH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	274.4
2.5°	272.9
5°	269.9
7.5°	263.8
10°	256.2
12.5°	246.8
15°	235.1
17.5°	222.6
20°	208.6
22.5°	194.3
25°	179.5
27.5°	164.8
30°	150.0
32.5°	134.2
35°	117.9
37.5°	102.0
40°	86.9
42.5°	70.7
45°	54.4
47.5°	41.6
50°	30.2
52.5°	19.7
55°	14.0
57.5°	12.5
60°	11.3
62.5°	10.2
65°	9.1
67.5°	7.9
70°	6.8
72.5°	5.7
75°	4.5
77.5°	3.8
80°	3.0
82.5°	1.9
85°	1.1
87.5°	0.8
90°	0.0

(END OF REPORT)