

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298310

Luminaire Tested: P3A13R60W2N902750DE010 E3DLP1H_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298310
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3A13R60W2N902750DE010 E3DLP1H_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLP1H TRIM
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 556.0 lumens
Efficiency: N/A
Efficacy: 45.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298310

CATALOG NUMBER: P3A13R60W2N902750DE010 E3DLP1H_3000K

Luminous Intensity Polar Plot



TEST NUMBER: P1298310

CATALOG NUMBER: P3A13R60W2N902750DE010 E3DLP1H_3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10		0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102		100
1	113	110	107	105	110	108	105	103	104	102	100		100	98	97		96	95	94		92
2	107	101	97	93	104	100	96	92	96	93	90		93	91	88		91	88	86		85
3	101	94	88	84	99	92	87	83	90	86	82		87	84	81		85	82	80		78
4	95	87	81	77	93	86	80	76	84	79	75		82	78	74		80	76	73		72
5	90	81	75	70	88	80	74	70	78	73	69		77	72	69		75	71	68		66
6	85	76	69	65	84	75	69	65	73	68	64		72	67	64		71	66	63		62
7	81	71	65	60	79	70	64	60	69	64	60		68	63	59		67	62	59		57
8	77	67	60	56	75	66	60	56	65	60	56		64	59	55		63	58	55		54
9	73	63	57	52	72	62	56	52	61	56	52		60	55	52		60	55	52		50
10	69	59	53	49	68	59	53	49	58	53	49		57	52	49		56	52	49		47

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140910
5°	137750
10°	128967
15°	115687
20°	99502
25°	82263
30°	64997
35°	48265
40°	33234
45°	20839
50°	11462
55°	6729
60°	6052
65°	5137
70°	4424
75°	4490
80°	3915
85°	3774

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 20839 cd/sqm

TEST NUMBER: P1298310

CATALOG NUMBER: P3A13R60W2N902750DE010 E3DLP1H_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.3	10.5
10°-20°	141.5	25.5
20°-30°	155.2	27.9
30°-40°	113.1	20.3
40°-50°	53.4	9.6
50°-60°	17.5	3.2
60°-70°	9.9	1.8
70°-80°	5.3	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	355.0	63.9
0°-40°	468.1	84.2
0°-60°	539.1	97.0
0°-90°	556.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	556.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	643	
5°	626	58
15°	510	142
25°	340	155
35°	180	113
45°	67	53
55°	18	18
65°	10	10
75°	5	5
85°	2	2
90°	0	

TEST NUMBER: P1298310

CATALOG NUMBER: P3A13R60W2N902750DE010 E3DLP1H_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	642.6
2.5°	638.8
5°	625.8
7.5°	605.9
10°	579.2
12.5°	547.1
15°	509.6
17.5°	469.1
20°	426.4
22.5°	382.8
25°	340.0
27.5°	297.2
30°	256.7
32.5°	217.8
35°	180.3
37.5°	146.7
40°	116.1
42.5°	89.4
45°	67.2
47.5°	48.9
50°	33.6
52.5°	22.2
55°	17.6
57.5°	15.3
60°	13.8
62.5°	11.5
65°	9.9
67.5°	8.4
70°	6.9
72.5°	6.1
75°	5.3
77.5°	3.8
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)